




PRODUCT CATALOG 2014



Worldwide Leader in Legacy Memory

Alliance Memory, Inc supports the full range of 3.3V and 5V Asynchronous SRAMs in densities from 64K up to 32Mb and with speeds offered in the range of 8-20ns (Fast Asynchronous) to 45-70ns (Low Power SRAMs) and ZBT/Sync Pipelined burst (SPB)/Sync Burst (SB) SRAMs. We also manufacture a complete line-up of DRAMs in densities of 16M, 64M, 128M, 256M, 512M, 1G, 2G, and 4G. These memories are used with mainstream digital signal processors (DSPs) and microcontrollers found mainly in the digital consumer electronics, networking, mobile communications, industrial, medical and the automotive electronics marketplace.



Fast Asynchronous SRAM



5V FAST ASYNCHRONOUS SRAM

DENSITY	ORG	VCC	PACKAGES	SPEED (NS)	ALLIANCE
64K	8K x 8	5V	SOJ (28pin)	15	AS7C164A
256K	32K x 8	5V	SOJ (28pin), TSOP I (28pin)	10/12/15/20	AS7C256A
512K	32K x 16	5V	SOJ (44), TSOP II (44)	10/12/15/20	AS7C513B
1M	128K x 8	5V	SOJ (32.3 & 32.4), TSOP I (32)	10/12/15/20	AS7C1024B
1M	128K x 8	5V	SOJ (32.3 & 32.4)	10/12/15/20	AS7C1025B
1M	64K x 16	5V	SOJ (44), TSOP II (44)	10/12/15/20	AS7C1026B
4M	512K x 8	5V	SOJ (36), TSOP II (44)	10/12/15/20	AS7C4096A
4M	256K x 16	5V	SOJ (44), TSOP II (44)	10/12/15/20	AS7C4098A

3.3V FAST ASYNCHRONOUS SRAM

DENSITY	ORG	VCC	PACKAGES	SPEED (NS)	ALLIANCE
256K	32K x 8	3.3V	SOJ (28), TSOP I (28)	10/12/15/20	AS7C3256A
512K	32K x 16	3.3V	SOJ (44), TSOP II (44)	10/12/15/20	AS7C3513B
1M	128K x 8	3.3V	SOJ (32.3 & 32.4), TSOP I (32)	10/12/15/20	AS7C31024B
1M	128K x 8	3.3V	SOJ (32.3 & 32.4)	10/12/15/20	AS7C31025B
1M	128K x 8	3.3V	SOJ (32.3 & 32.4), TSOP II (32)	10/12	AS7C31025C
1M	64K x 16	3.3V	SOJ (44), TSOP II (44)	10/12/15/20	AS7C31026B
2M	128K x 16	3.3V	TSOP II (44)	10/12/15/20	AS7C32098A
4M	512K x 8	3.3V	SOJ (36), TSOP II (44)	8/10/12/15/20	AS7C34096A
4M	256K x 16	3.3V	SOJ (44), TSOP II (44), TFBGA (48)	8/10/12/15/20	AS7C34098A
8M	1024K x 8	3.3V	TFBGA (48), TSOP II (44)	10	AS7C38096A
8M	512K x 16	3.3V	TFBGA (48), TSOP II (44)	10	AS7C38098A
16M	2M x 8	3.3V	TFBGA (48), TSOP I (48)	10	AS7C316096A
16M	1024K x 16	3.3V	TFBGA (48), TSOP I (48)	10	AS7C316098A

Fast Asynchronous SRAM Cross Reference



64K FAST

ORG	VCC	PACKAGE	SPEED (NS)	ALLIANCE	SAMSUNG	CYPRESS	IDT	ISSI	GSI
8K x 8	5v	28pin SOJ (300mil)	15	AS7C164A-XXJCN		CY7C185-15VI	IDT7164SXXYG	IS61C64AL-XXJLI	

256K FAST

ORG	VCC	PACKAGE	SPEED (NS)	ALLIANCE	SAMSUNG	CYPRESS	IDT	ISSI	GSI
32K x 8	5v	28pin SOJ	10,12,15,20	AS7C256A-XXJCN	K6E0808C (EOL)	CY7C199D-XXVXI	IDT71256SAXXYG	IS61C256AL-XXJL	
32K x 8	5v	28pin TSOP I	10,12,15,20	AS7C256A-XXTCN		CY7C199D-XXZXI	IDT71256SAXXPZG	IS61C256AL-XXTL	
32K x 8	3.3v	28pin SOJ	10,12,15,20	AS7C3256A-XXJCN	K6E0808V (EOL)	CY7C1399BN-12VXC	IDT71V256SAXXYG	IS61LV256AL-10JL	
32K x 8	3.3v	28pin TSOP I	10,12,15,20	AS7C3256A-XXTCN		CY7C1399BN-XXZXI	IDT71V256SAXXPZG	IS61LV256AL-10TL	
32K x 8	5v	28pin DIP	20	AS7C256B-XXPIN		CY7C199CN-XXPXC	IDT71256SAXXTPG		

512K FAST

ORG	VCC	PACKAGE	SPEED (NS)	ALLIANCE	SAMSUNG	CYPRESS	IDT	ISSI	GSI
32K x 16	5v	44pin SOJ (400MIL)	12,15,20	AS7C513B-XXJCN		CY7C1020D-10VXI		IS61C321AL-12KLI	
32K x 16	5v	44pin TSOP II (400MIL)	12,15,20	AS7C513B-XXTCN		CY7C1020D-10ZSXI		IS61C3216AL-12TLI	
32K x 16	3.3v	44pin TSOP II (400MIL)	12,15,20	AS7C3513B-XXTCN		CY7C1020DV33-10ZSXI		IS61WV3216BLL-12TLI	
32K x 16	3.3v	44pin SOJ (400MIL)	12,15	AS7C3513B-XXJCN		CY7C1020DV33-10VXI			

1M FAST

ORG	VCC	PACKAGE	SPEED (NS)	ALLIANCE	SAMSUNG	CYPRESS	IDT	ISSI	GSI
128K x 8	5v	32pin SOJ (400MIL)	12,15,20	AS7C1025B-XXJCN	K6R1008C1D-KI10	CY7C1019D-10VXI	IDT71124SXXYG		
128K x 8	3.3v	32pin SOJ (400MIL)	10,12,15,20	AS7C31025B-XXJCN	K6R1008V1D-KI10	CY7C1019DV33-10VXI	IDT71V124SAXXYG	IS63WV1024L-10KLI	
128K x 8	3.3v	32pin TSOP II	10	AS7C31025C-10TIN	K6R1008V1D-UI10	CY7C1019DV33-10ZSXI	IDT71V124SAXXPHG	IS63WV1288DBLL10TLI	
128K x 8	5v	32pin SOJ (300MIL)	10,12,15,20	AS7C1025B-XXTJCN					
128K x 8	3.3v	32pin SOJ (300MIL)	10,12,15,20	AS7C31025B-XXTJCN		CY7C1018DV33-10VXI	IDT71V124SAXXTYG	IS63WV1288DBLL-10JLI	
128K x 8	5v	32pin SOJ (400MIL)	10,12,15,20	AS7C1024B-XXJCN		CY7C109D-10VXI	IDT71024SXXYG	IS61C1024AL-12KLI	
128K x 8	5v	32pin TSOP I	10,12,15,20	AS7C1024B-XXTCN		CY7C109D-10ZXI		IS61C1024AL-12TLI	
128K x 8	5v	32pin SOJ (300MIL)	10,12,15,20	AS7C1024B-XXTJCN		CY7C1009D-10VXI	IDT71024SXXTYG	IS61C1024AL-12JLI	
128K x 8	3.3v	32pin SOJ (400MIL)	10,12,15,20	AS7C31024B-XXJCN					
128K x 8	3.3v	32pin TSOP I	10,12,15,20	AS7C31024B-XXTCN					
128K x 8	3.3v	32pin SOJ (300MIL)	10,12,15,20	AS7C31024B-XXTJCN					
64K x 16	5v	44pin SOJ (400MIL)	10,12,15,20	AS7C1026B/C-XXJCN	K6R1016C1D-KI10	CY7C1021D-XXVXC	IDT71016SXXYG	IS61C6416AL-12KLI	
64K x 16	5v	44pin TSOP II (400MIL)	10,12,15,20	AS7C1026B/C-XXTCN	K6R1016C1D-UI10	CY7C1021D-XXZSXI	IDT71016SXXPHG	IS61C6416AL-12TLI	
64K x 16	3.3v	44pin SOJ (400MIL)	10,12,15,20	AS7C31026B/C-XXJCN	K6R1016V1D-KI10	CY7C1021DV33-XXVXI	IDT71V016SAXXYG	IS61WV6416DBLL-10KLI	
64K x 16	3.3v	44pin TSOP II (400MIL)	10,12,15,20	AS7C31026B/C-XXTCN	K6R1016V1D-UI10	CY7C1021DV33-XXZSXI	IDT71V016SAXXPHG	IS61WV6416DBLL-10TLI	GS71116AGP-XX

Fast Asynchronous SRAM Cross Reference



2M FAST

ORG	VCC	PACKAGE	SPEED (NS)	ALLIANCE	SAMSUNG	CYPRESS	IDT	ISSI	GSI
128K x 16	3.3v	44pin TSOP II	10,12,15,20	AS7C32098A-XXTCN		CY7C1011DV33-10ZSXI		IS61WV12816DBLL-10TL	GS72116AGP-XX
256K x 8	3.3v	44pin TSOP II	10,12,15,20	AS7C32096A-10TCN		CY7C1010DV33-10ZSXI		IS61WV256EDBL-10TLI	GS72108AGP-XX

4M FAST

ORG	VCC	PACKAGE	SPEED (NS)	ALLIANCE	SAMSUNG	CYPRESS	IDT	ISSI	GSI
512K x 8	5v	36pin SOJ (400MIL)	12,15,20	AS7C4096A-XXJCN	K6R4008C1D-KI10	CY7C1049D-10VXI		IS61C5128AL-10KLI	
512K x 8	5v	44pin TSOP II (400MIL)	12,15,20	AS7C4096A-XXTCN	K6R4008C1D-UI10			IS61C5128AL-10TLI	
512K x 8	3.3v	36pin SOJ (400MIL)	10,12,15,20	AS7C34096A-XXJCN	K6R4008V1D-KI10	CY7C1049DV33-10VXI	IDT71V424SXXYG	IS61WV5128EDBL-10KLI	
512K x 8	3.3v	44pin TSOP II (400MIL)	8,10,12,15,20	AS7C34096A-XXTCN	K6R4008V1D-UI10	CY7C1049DV33-10ZSI	IDT71V424SXXPHG	IS61WV5128EDBL-10TLI	GS74108AGP-XX
256K x 16	5v	44pin SOJ (400MIL)	12,15,20	AS7C4098A-XXJCN	K6R4016C1D-KI10	CY7C1041D-10VXI		IS61C25616AL-10KLI	
256K x 16	5v	44pin TSOP II (400MIL)	12,15,20	AS7C4098A-XXTCN	K6R4016C1D-UI10	CY7C1041D-10ZSXI		IS61C25616AL-10TL	
256K x 16	3.3v	44pin SOJ (400MIL)	10,12,15,20	AS7C34098A-XXJCN	K6R4016V1D-KI10	CY7C1041DV33-10VXI	IDT71V416SXXYG	NA	
256K x 16	3.3v	44pin TSOP II (400MIL)	8,10,12,15,20	AS7C34098A-XXTCN	K6R4016V1D-UI10	CY7C1041DV33-10ZSXI	IDT71V416SXXPHG	IS61WV25616EDBL-10TLI	GS74116AGP-XX
256K x 16	3.3v	48ball TFBGA	10	AS7C34098A-XXBIN		CY7C1041DV33-10BVXI	IDT71V416SXXBE	IS61WV25616EDBL-10BLI	GS75116AGX-XX

8M FAST

ORG	VCC	PACKAGE	SPEED (NS)	ALLIANCE	SAMSUNG	CYPRESS	IDT	ISSI	GSI
512K x 16	3.3v	44pin TSOP II	10	AS7C38098A-10TIN		CY7C1051DV33-XXZSXI		IS61WV51216ALL-XXTLI	
512K x 16	3.3v	48ball TFBGA	10	AS7C38098A-10BIN		CY7C1051DV33-XXZSXI		IS61WV51216ALL-10MLI	
1024K x 8	3.3v	44pin TSOP II	10	AS7C38096A-10TIN		CY7C1059DV33-10ZSXI		IS61WV10248BL-10TLI	
1024K x 8	3.3v	48ball TFBGA	10	AS7C38096A-10BIN				IS61WV10248BL-10MLI	

16M FAST

ORG	VCC	PACKAGE	SPEED (NS)	ALLIANCE	SAMSUNG	CYPRESS	IDT	ISSI	GSI
1024K x 16	3.3v	48pin TSOP I	10	AS7C316098A-10TIN				IS61WV102416BL-10TLI	
1024K x 16	3.3v	48ball TFBGA	10	AS7C316098A-10BIN		CY7C1069DV33-10BVXIT		IS61WV102416BL-10MLI	
2M x 8	3.3v	48pin TSOP I	10	AS7C316096A-10TIN				IS61WV20488BL-10TLI	

Low Power Asynchronous SRAM



2.7V - 3.6V LOW POWER SRAMS

DENSITY	ORG	VCC	PACKAGES	SPEED (NS)	ALLIANCE
256K	32K x 8	2.4 ~ 3.6V	28pin SOP (330mm)	70	AS62V256A-70SIN
2M	256K x 8	3V	32pin 450 mil SOP	55	AS6C2008-55SIN
2M	256K x 8	3V	32pin TSOP I (8 x 20mm)	55	AS6C2008-55TIN
2M	256K x 8	3V	32pin STSOP (8 x 13.4mm)	55	AS6C2008-55STIN
2M	256K x 8	3V	36pin TFBGA (6 x 8mm)	55	AS6C2008-55BIN
4M	512K x 8	2.7 ~ 3.6V	32pin TSOP I (8 x 20mm)	55	AS6C4008A-55TIN
4M	512K x 8	2.7 ~ 3.6V	32pin TSOP II (8 x 20mm)	55	AS6C4008A-55ZIN
4M	512K x 8	2.7 ~ 3.6V	32pin STSOP (8 x 13.4mm)	55	AS6C4008A-55STIN
4M	512K x 8	2.7 ~ 3.6V	36pin TFBGA (6 x 8mm)	55	AS6C4008A-55BIN
4M	256K x 16	2.7 ~ 3.6V	44pin TSOP II	45/55	AS6C4016A-55ZIN
4M	256K x 16	2.7 ~ 3.6V	48ball TFBGA (6 x 8mm)	45/55	AS6C4016A-55BIN/45BIN
8M	1M x 8	2.7 ~ 3.6V	44pin TSOP II	55	AS6C8008A-55ZIN
8M	1M x 8	2.7 ~ 5.5V	48ball TFBGA (6 x 8mm)	45	AS6C8008A-55BIN
8M	512K x 16	2.7 ~ 3.6V	44pin TSOP II	55	AS6C8016A-55ZIN
8M	512K x 16	2.7 ~ 3.6V	48ball TFBGA (6 x 8mm)	55	AS6C8016A-55BIN
16M	1M x 16	2.7 ~ 3.6V	48ball TFBGA (6 x 8mm)	55/70	AS6C1616-70BIN
16M	1M x 16	2.7 ~ 3.6V	48ball TFBGA (6 x 8mm)	55	AS6C1616A-55BIN
16M	1M x 16	2.7 ~ 3.6V	48pin TSOP I (12 x 20mm)	55	AS6C1616-55TIN
16M	2M x 8	2.7 ~ 3.6V	44pin TSOP II	55	AS6C1608-55TIN
32M	2M x 16	2.7 ~ 3.6V	48pin TSOP I (12 x 20mm)	55	AS6C3216-55TIN
32M	2M x 16	2.7 ~ 3.6V	48ball TFBGA (6 x 8mm)	55	AS6C3216-55BIN

2.7V - 5.5V LOW POWER SRAMS

DENSITY	ORG	VCC	PACKAGES	SPEED (NS)	ALLIANCE
64K	8K x 8	2.7 ~ 5.5V	28pin 600 mil PDIP, 28pin 330 mil SOP, 28pin sTSP (8x13.4mm)	55	AS6C6264
64K	8K x 8	4.5 - 5.5V	28pin 600 mil PDIP, 28pin 330 mil SOP	70	AS6C6264A
256K	32K x 8	2.7 ~ 5.5V	28pin 600 mil PDIP, 28pin 330 mil SOP, 28pin sTSP (8x13.4mm)	55	AS6C62256
256K	32K x 8	4.5 - 5.5V	28pin 600 mil PDIP, 28pin 330 mil SOP	70	AS6C62256A
1M	64K x 16	2.7 ~ 5.5V	44pin 400 mil TSOP II TFBGA (48)	55	AS6C1016
1M	128K x 8	2.7 ~ 5.5V	32pin 450 mil SOP, 32pin TSOP I (8 x 20mm), 32pin sTSP (8 x 13.4mm), TFBGA (36), 32pin PDIP	55	AS6C1008
2M	256K x 8	2.7 ~ 5.5V	32pin 450 mil SOP, 32pin TSOP I (8 x 20mm) 32pin sTSP (8 x 13.4mm), TFBGA (36)	55	AS6C2008A
2M	128K x 16	2.7 ~ 5.5V	44pin 400 mil TSOP II, TFBGA (48)	55	AS6C2016

Low Power Asynchronous SRAM



2.7V - 5.5V LOW POWER SRAMS

DENSITY	ORG	VCC	PACKAGES	SPEED (NS)	ALLIANCE
4M	512K x 8	2.7 ~ 5.5V	32pin 450 mil SOP, 32pin TSOP I (8 x 20mm), 32pin sTSOP (8 x 13.4mm), TFBGA (36), 32pin 600 mil PDIP, 32pin TSOP II	55	AS6C4008
4M	256K x 16	2.7 ~ 5.5V	44pin TSOP II, TFBGA (48)	55	AS6C4016
8M	1024K x 8	2.7 ~ 5.5V	44pin TSOP II, TFBGA (48)	55	AS6C8008
8M	512K x 16	2.7 ~ 5.5V	44pin TSOP II, TFBGA (48)	55	AS6C8016

ZMD Low Power Asynchronous SRAM

5V LOW POWER SRAMS

DENSITY	ORG	VCC	PACKAGES	SPEED (NS)	ZMD PART NUMBER
64K	8K x 8	4.5 ~ 5.5V	28pin 600 mil PDIP	70	U6264BD
64K	8K x 8	4.5 ~ 5.5V	28pin 330 mil SOP	70	U6264BS2
256K	32K x 8	4.5 ~ 5.5V	28pin 600 mil PDIP	70	U62256AD
256K	32K x 8	4.5 ~ 5.5V	28pin 330 mil SOP	70	U62256AS2

Low Power Asynchronous SRAM Cross Reference



64K LOW POWER

ORG	VCC	PACKAGE	ALLIANCE	ZMD	CYPRESS	HITACHI	NEC	HYNIX
8K x 8	5V	28pin 600mil DIP	AS6C6264-55PCN	U6264BDC07LLG1		HM6264BLP		HY6264P
8K x 8	5V	28pin 330mil SOP	AS6C6264-55SCN	U6264BS2C07LLG1	CY6264-55SNXI	HM6264BLFP	uPD4464	HY6264G
8K x 8	5V	28pin STSOP (8 x 13.4 mm)	AS6C6264-55STCN					

256K LOW POWER

ORG	VCC	PACKAGE	ALLIANCE	ZMD	SAMSUNG	CYPRESS	RENESAS	BRILLIANCE	ISSI
32K x 8	5V	28pin 600mil DIP	AS6C62256-55PCN	U62256ADC07LLG1	K6X0808C1D-DF55	CY62256NLL-70PXC		BS62LV256PCP-55	
32K x 8	5V	28pin 330mil SOP	AS6C62256-55SCN	U62256AS2C07LLG1	K6X0808C1D-BF55	CY62256NLL-55SNXI	M5M5256DFP	BS62LV256SCP-55	IS62C256AL-45ULI
32K x 8	3.3V	28pin 330mil SOP	AS6C62256-55SCN			CY62256NVLL-70SNXI	M5M5256DFP-70XG	BS62LV256SCP-55	IS62LV256AL-45ULI
32K x 8	5V	28pin STSOP (8 x 13.4 mm)	AS6C62256-55STCN		K6X0808C1D-LF55	CY62256NLL-55ZRXI	M5M5256DVP-55XL	BS62LV256STCP-55	IS62C256AL-45TLI
32K x 8	3.3V	28pin STSOP (8 x 13.4 mm)	AS6C62256-55STCN			CY62256NVLL-70ZXC	M5M5256DVP-70XG	BS62LV256STCP-55	IS62LV256AL-45TLI

1M LOW POWER

ORG	VCC	PACKAGE	ALLIANCE	SAMSUNG	CYPRESS	RENESAS	RENESAS	BRILLIANCE	NEC	ISSI
128K x 8	5V	32pin 600mil DIP	AS6C1008-55PCN	K6X1008C2D-DB55				BS62LV1027PCP-55	uPD431000ACZ-70L	
128K x 8	5V	32pin 330mil SOP	AS6C1008-55SIN	K6X1008C2D-GF55(Lead)/BF(LF)	CY62128ELL-45SXI	M5M51008DFP-55HI	R1LP0108ESP-5SI	BS62LV1027SIP-55	uPD431000AGW-70L	IS62C1024AL-35QLI
128K x 8	3.3V	32pin 330mil SOP	AS6C1008-55SIN	K6X1008T2D-GF55 or BF	CY62128EV30LL-45SXI	M5M5V108DFP-70HI	R1LV0108ESP-5SI	BS62LV1027SIP-55		IS62WV1288DBLL-45QLI
128K x 8	5V	32pin TSOP I (8 x 20 mm)	AS6C1008-55TIN	K6X1008C2D-TF55 or PF	CY62128ELL-45ZXI	M5M51008DVP-55HI	R1LP0108ESF-5SI	BS62LV1027TIP-55	uPD431000AGZ-70LL-KKH	IS62C1024AL-35TLI
128K x 8	3.3V	32pin TSOP I (8 x 20 mm)	AS6C1008-55TIN	K6X1008T2D-TF55(Lead)/PF(LF)	CY62128EV30LL-45ZXI	M5M5V108DVP-70HI	R1LV0108ESF-5SI	BS62LV1027TIP-55		IS62WV1288DBLL-45TLI
128K x 8	5V	32pin STSOP (8 x 13.4 mm)	AS6C1008-55STIN		CY62128ELL-45ZAXI	M5M51008DKV-55HI	R1LP0108ESA-5SI	BS62LV1027STIP-55	uPD431000AGU-B10-9JH	IS62C1024AL-45HLI
128K x 8	3.3V	32pin STSOP (8 x 13.4 mm)	AS6C1008-55STIN	K6F1008V2C-LF55	CY62128EV30LL-45ZAXI	M5M5V108DKV-70HI	R1LV0108EAS-5SI	BS62LV1027STIP-55		IS62WV1288DBLL-45HLI
64K x 16	3.3V	44pin TSOP II	AS6C1016-55ZIN		CY62128EV30LL-45ZSXI			BS616LV1010ECP-55		IS62WV6416DBLL-45TLI

2M LOW POWER

ORG	VCC	PACKAGE	ALLIANCE	SAMSUNG	CYPRESS	RENESAS	RENESAS	BRILLIANCE	ISSI
256K x 8	3.3v	32pin 450mil SOP	AS6C2008-55SIN		CY62138FV30LL-45SXI			BS62LV2006SIP-55	
256K x 8	3.3v	32pin TSOP I (8 x 20 mm)	AS6C2008-55TIN		CY62138FV30LL-45ZXI			BS62LV2006TIP-55	
256K x 8	3.3v	32pin STSOP (8 x 13.4 mm)	AS6C2008-55STIN	K6F2008V2E-LF70000	CY62138FV30LL-45ZAXI	M5M5V208AKV-55HI	R1LV0208BSA-5SI	BS62LV2006STIP-55	IS62WV2568BLL-55HLI
256K x 8	3.3v	36pin TFBGA (6mm x 8mm)	AS6C2008-55BIN		CY62138FV30LL-45BVXI				IS62WV2568BLL-55B2LI
128K x 16	3V	44pin TSOP II	AS6C2016-55ZIN		CY62136FVLL-70ZSXI	M5M5V216ATP-70HI	R1LV0216-BSB-5SI	BS616LV2016EIP-55	IS62WV12816BLL-55TLI
128K x 16	3V	48 BGA	AS6C2016-55BIN	K6F2016U4E-EF55000	CY62136FVLL-70BVXI			BS616LV2019AIG-55	IS62WV12816BLL-55B2LI

Low Power Asynchronous SRAM Cross Reference



4M LOW POWER

ORG	VCC	PACKAGE	ALLIANCE	SAMSUNG	CYPRESS	RENESAS	BRILLIANCE	NEC	ISSI
512K x 8	5V	32pin 600mil DIP	AS6C4008-55PCN	K4X4008C1F-DB55			BS62LV4006PCP-55		
512K x 8	5V	32pin 450mil SOP	AS6C4008-55SIN	K6X4008C1F-GF55 or BF	CY62148ELL-55SXI	R1LV0408CSP-5SI	BS62LV4006SIP-55		IS62C5128BLL-45QLI
512K x 8	3.3V	32pin 450mil SOP	AS6C4008A-55SIN	K6X4008T1F-GF55 or BF	CY62148EV30LL-55SXI	R1LV0408CSP-5SI	BS62LV4006SIP-55		IS62WV5128DBLL-45QLI
512K x 8	5V	32pin TSOP I (8 x 20mm)	AS6C4008A-55TIN				BS62LV4006ECP-55		
512K x 8	5V	32pin STSOP (8 x 13.4mm)	AS6C4008-55STIN		CY62148ELL-55ZAXI	R1LV0408DSA-5SI	BS62LV4006STIP-55		IS62C5128BL-45HLI
512K x 8	3.3V	32pin STSOP (8 x 13.4mm)	AS6C4008A-55STIN	K6X4008T1F-YF55 or LF	CY62148EV30LL-55ZAXI	R1LV0408DSA-5SI	BS62LV4006STIP-55		IS62WV5128DBLL-45HLI
512K x 8	5V	32pin TSOP II	AS6C4008-55ZIN	K6X4008C1F-VF55	CY62148ELL-45ZSXI	R1LV0408DSB-5SI	BS62LV4006ECP55		IS62WV5128DBLL-45T2LI
512K x 8	3.3V	32pin TSOP II	AS6C4008A-55ZIN		CY62148DV30				IS62WV5128DBLL-55T2LI
512K x 8	5V	36pin TFBGA (6mm x 8mm)	AS6C4008-55BIN		CY62148EV30LL-55BVXI	R1LV0408DBG-5SI			
512K x 8	3.3V	36pin TFBGA (6mm x 8mm)	AS6C4008A-55BIN		CY62148DV30-55BVXI	R1LV0408DBG-5SI	BS62LV4006HIG-55		
256K x 16	5V	44pin TSOP II	AS6C4016-55ZIN	K6X4016C3F-TF70000	CY62146ELL-45ZSXI		BS616LV4017EIP-55		IS62C5128BL-45TLI
256K x 16	3.3V	44pin TSOP II	AS6C4016A-55ZIN	K6X4016T3F-TF70000	CY62147EV30LL-45ZSXI	R1LV0414DSB-5SI	BS616LV4017EIP-55	upD444012AGY-B55X	IS62C25616BL-45T2LI
256K x 16	3.3V	48 BGA	AS6C4016A-55BIN	K6F4016U6G-EF70000	CY62147EV30LL-45BVXI		BS616LV4017AIP-55		IS62WV25616DBLL-45BLI

8M LOW POWER

ORG	VCC	PACKAGE	ALLIANCE	SAMSUNG	CYPRESS	RENESAS	RENESAS	RENESAS	BRILLIANCE	NEC	ISSI
1024K x 8	2.7 ~ 5.5V	44pin TSOP II	AS6C8008-55ZIN	K6X8008(C/T)2B-UF55	CY62158EV30LL-45ZSXI		R1LV0808ASB-5SI	HM62V8100LTTI-5SL	BS62LV8001ECP-55		IS62WV1024BLL-55TLI
1024K x 8	2.7 ~ 5.5V	48ball TFBGA	AS6C8008-55BIN		CY62158EV30LL-45BVXI	EOL					IS62WV1024BLL-55MLI
512K x 16	2.7 ~ 5.5V	48ball TFBGA	AS6C8016-55BIN	K6F8016U6G-FF55	CY62157EV30LL-55BVXI	M5M5W816WG-55HI	R1LV0816ABG-5SI		BS616LV8017ECP55		IS62WV51216BLL-55BLI
512K x 16	2.7 ~ 5.5V	44pin TSOP II	AS6C8016-55ZIN	K6X8016(C/T)3B-UF55	CY62157EV30LL-55ZSXI	M5M5W816TP-55HI	R1LV0816ASA-5SI	HM62165114LTT-5SL	BS616LV8017FCP70	μPD448012GY-B55X-MJH-A	IS62WV51216BLL-55T2LI

16M LOW POWER

ORG	VCC	PACKAGE	ALLIANCE	SAMSUNG	CYPRESS	RENESAS	BRILLIANCE
1024K x 16	2.7 ~ 3.6V	48ball TFBGA	AS6C1616-70BIN	K6F1616U6C-FF70	CY62167EV30LL-70BVI	R1LV1616RBG-7SI	BS2616LV1611FCP70
1024K x 16	2.7 ~ 3.6V	48pin TSOP I	AS6C1616-55TIN		CY62167E30LL-55ZXI	R1LV1616RSA-5SI	BS2616LV1611TCP55

32M LOW POWER

ORG	VCC	PACKAGE	ALLIANCE	CYPRESS	RENESAS
2048K x 16	2.7 ~ 3.6V	48pin TSOP I	AS6C3216-55TIN	CY62177EV30LL-55ZXI	R1LV3216RSA-5SI
2048K x 16	2.7 ~ 3.6V	48ball TFBGA	AS6C3216-55BIN	CY62177EV30LL-55BXI	R1LV3216CSA-5SI

ZBT/Sync Pipelined Burst (SPB)/Sync Burst (SB)



SYNC SRAM

DENSITY	ORG	VCC	PACKAGE	MODE	SPEED (MHz)	ALLIANCE
4M	256K x 18	3.3V	100 TQFP	ZBT/SPB	166 MHz	AS8C401801-QC166N
4M	128K x 36	3.3V	100 TQFP	ZBT/SPB	166 MHz	AS8C403601-QC166N
4M	256K x 18	3.3V	100 TQFP	SPB	150 MHz	AS8C401800-QC150N
4M	128K x 36	3.3V	100 TQFP	SPB	150 MHz	AS8C403600-QC150N
4M	256K x 18	3.3V	100 TQFP	SB	7.5NS	AS8C401825-QC75N
4M	128K x 36	3.3V	100 TQFP	SB	7.5NS	AS8C403625-QC75N
9M	512K x 18	3.3V	100 TQFP	ZBT/SPB	150 MHz	AS8C801801-QC150N
9M	256K x 36	3.3V	100 TQFP	ZBT/SPB	150 MHz	AS8C803601-QC150N
9M	512K x 18	3.3V	100 TQFP	ZBT/SB	7.5NS	AS8C801825A-QC75N
9M	256K x 36	3.3V	100 TQFP	ZBT/SB	7.5NS	AS8C803625A-QC75N
9M	512K x 18	3.3V	100 TQFP	SPB	150 MHz	AS8C801800-QC150N
9M	256K x 36	3.3V	100 TQFP	SPB	150 MHz	AS8C803600-QC150N
9M	512K x 18	3.3V	100 TQFP	SB	7.5NS	AS8C801825-QC75N
9M	256K x 36	3.3V	100 TQFP	SB	7.5NS	AS8C803625-QC75N
18M	1M x 18	2.5V	100 TQFP	ZBT/SPB	166 MHz	AS8C161831-QC166N
18M	512K x 36	2.5V	100 TQFP	ZBT/SPB	166 MHz	AS8C163631-QC166N

Sync SRAM Cross Reference



4M

PACKAGE	MODE	ALLIANCE	IDT	SAMSUNG	CYPRESS	GSi	ISSI
100TQFP	SPB	AS8C403600-QC150N	71V3576SxxxPFG	K7A403600B-QCxx	CY7C1347G-xxxAX	GS84036AGT-xxx	IS61LPS12836A-xxxTQ
		AS8C401800-QC150N	71V3578SxxxPFG	K7A401800B-QCxx	CY7C1327G-xxxAX	GS84018AGT-xxx	IS61LPS25618A-xxxTQ
	SB	AS8C403625-QC75N	71V3577SxxPFG	K7B403625B-QCxx	CY7C1345G-xxxAX	GS84036AGT-xxx	IS61LF12836A-xxxTQ
		AS8C401825-QC75N	71V3579SxxPFG	K7B401825B-QCxx	CY7C1325G-xxxAX	GS84018AGT-xxx	IS61LF25618A-xxxTQ
	ZBT/SPB	AS8C403601-QC166N	71V3556SxxxPFG	K7N403601B-QCxx	CY7C1350G-xxxAX	GS840Z36AGT-xxx	IS61NLP12836A-xxxTQ
		AS8C401801-QC166N	71V3558SxxxPFG	K7N401801B-QCxx	CY7C1352G-xxxAX	GS840Z18AGT-xxx	IS61NLP25618A-xxxTQ

9M

PACKAGE	MODE	ALLIANCE	IDT	SAMSUNG	CYPRESS	GSi	ISSI
100TQFP	SPB	AS8C803600-QC150N	71V67603SxxxPFG	K7A803600B-QCxx	CY7C1360C-xxxAJX	GS88036CT-xxx	IS61LPS25636A-xxxTQ
		AS8C801800-QC150N	71V67803SxxxPFG	K7A801800B-QCxx	CY7C1362C-xxxAJX	GS88018CT-xxx	IS61LPS51218A-xxxTQ
	SB	AS8C803625-QC75N	71V67703SxxPFG	K7B803625B-QCxx	CY7C1361C-xxxAJX	GS88036CT-xxx	IS61LPS25636A-xxxTQ
		AS8C801825-QC75N	71V67903SxxPFG	K7B801825B-QCxx	CY7C1363C-xxxAJX	GS88018CT-xxx	IS61LPS51218A-xxxTQ
	ZBT/SPB	AS8C803601-QC150N	71V65603SxxxPFG	K7N803601B-QCxx	CY7C1354C-xxxAJX	GS880Z36CT-xxx	IS61NLP25636A-xxxTQ
		AS8C801801-QC150N	71V65803SxxxPFG	K7N801801B-QCxx	CY7C1356C-xxxAJX	GS880Z18CT-xxx	IS61NLP51218A-xxxTQ
	ZBT/SB	AS8C803625A-QC75N	71V65703SxxPFG	K7M803625B-QCxx	CY7C1351C-xxxAJX	GS880Z36CT-xxx	N/A
		AS8C801825A-QC75N	71V65903SxxPFG	K7M801825B-QCxx	CY7C1353C-xxxAJX	GS880Z18CT-xxx	N/A

18M

PACKAGE	MODE	ALLIANCE	IDT	SAMSUNG	CYPRESS	GSi	ISSI
100TQFP	ZBT/SPB	AS8C163631-QC166N	71T75602SxxxPFG	K7N163631B-QCxx	CY7C1370D-xxxAX	GS880Z36CT-xxx	IS61LPS12836A-xxxTQ
		AS8C161831-QC166N	71T75802SxxxPFG	K7N161831B-QCxx	CY7C1372D-xxxAX	GS880Z18CT-xxx	IS61LPS102418A-xxxTQ

Synchronous DRAM (SDR) x16 and x32



DENSITY	ORG	VCC	PACKAGE	SPEED (MHz)	TEMPERATURE	ALLIANCE
16Mb	1M x 16	3.3V	50pin TSOP II	143/166 MHz	Commercial, Industrial	AS4C1M16S-6/7TxN
64Mb	4M x 16	3.3V	54pin TSOP II	143/166 MHz	Commercial, Industrial, Automotive	AS4C4M16S-6/7TxN
64Mb	4M x 16	3.3V	54-ball BGA	143/166 MHz	Commercial, Industrial, Automotive	AS4C4M16S-6/7BxN
64Mb	2M x 32	3.3V	90-ball BGA	143/166 MHz	Commercial, Industrial	AS4C2M32S-6/7BxN
64Mb	2M x 32	3.3V	86pin TSOP II	143/166 MHz	Commercial, Industrial	AS4C2M32S-6/7TxN
128Mb	8M x 16	3.3V	54pin TSOP II	143/166 MHz	Commercial, Industrial, Automotive	AS4C8M16S-6/7TxN
128Mb	8M x 16	3.3V	54-ball FBGA	143/166 MHz	Commercial, Industrial	AS4C8M16S-6/7BxN
128Mb	4M x 32	3.3V	90-ball BGA	143/166 MHz	Commercial, Industrial	AS4C4M32S-6/7BxN
128Mb	4M x 32	3.3V	86pin TSOP II	143/166 MHz	Commercial, Industrial	AS4C4M32S-6/7TxN
256Mb	16M x 16	3.3V	54pin TSOP II	143/166 MHz	Commercial, Industrial, Automotive	AS4C16M16S-6/7TxN
256Mb	16M x 16	3.3V	54-ball FBGA	143/166 MHz	Commercial, Industrial	AS4C16M16S-6/7BxN
256Mb	8M x 32	3.3V	90-ball FBGA	143/166 MHz	Commercial, Industrial	AS4C8M32S-6/7BxN
512Mb	32M x 16	3.3V	54pin TSOP II	143/166 MHz	Commercial, Industrial	AS4C32M16SA-6/7TxN

Synchronous DRAM Cross Reference

DENSITY	ORG	ALLIANCE	SAMSUNG	MICRON	SK HYNIX	ISSI	WINBOND	NANYA	ETRON	INFINEON	ELPIDA
16Mb	1M x 16	AS4C1M16S-6/7TxN	K4S161622E	MT48LC1M16A1	HY57V161610E	IS42S16100F	W9816G6TH	NT56V1616AOT	EM636165TS	HYB39S16160CT	EDS1616AGTA
64Mb	4M x 16	AS4C4M16S-6/7TxN	K4S641632N-UCxx	MT48LC4M16A2P-xxD	HY57V641620ET-xxX	IS42S16400E-xxT	W9864G6JH-xx	NT56V6620C0T-xxB	EM638165TS-xx	HYB39S64160-xx	uPD4564163G5-Axx
64Mb	2M x 32	AS4C2M32S-7BCN		MT48LC2M32B2B5-x	HY5V62CF	IS42S32200L-xBL	W9864G2IB-x		EM638325B-xx		EDS6432AFBH
64Mb	2M x 32	AS4C2M32S-7TCN		MT48LC2M32B2P-x	HY57V643220CT	IS42S32200L-xTL	W9864G2JH-x		EM638325TS		EDS6432AFTA
128Mb	8M x 16	AS4C8M16S-6/7TxN	K4S281632K-UCxx	MT48LC8M16A2P-xxD	H57V1262GTR-xxX	IS42S16800D-xxT	W9812G6JH-xx	NT5SV8M16AT-xxB	EM639165TS-xx	HYB39S128160-xx	uPD45128163G5-Axx
128Mb	8M x 16	AS4C8M16S-7BCN	K4S281632D-RL75	MT48LC8M16A2B4-75		IS42S16800F-7BLA	W9812G6JB75		EM639165BM-xx		
128Mb	4M x 32	AS4C4M32S-7BCN		MT48LC4M32B2B5-x	HY5V22EM	IS42S32400F-xBL	W9812G21B-x		EM639325BM-xx		EDS1232AHBH
128Mb	4M x 32	AS4C4M32S-7TCN		MT48LC4M32B2P-x	HY57V283220T	IS42S32400F-xTL	W9812G21H-x		EM639325TS		EDS1232AHTA
256Mb	16M x 16	AS4C16M16S-6/7TxN	K4S561632N-UCxx	MT48LC16M16A2P-xxD	H57V2562GTR-xxX	IS42S16160D-xxT	W9825G6JH-xx	NT5SV16M16AT-xxB	EM63A165TS-xx	HYB39S256160-xx	EDS2516APTA-xx
256Mb	16M x 16	AS4C16M16S-7BCN	K4S561632D-RL75	MT48LC16M16A2B4-75		IS42S16160G-7BLA	W9825G6JB75		EM63A165BM-xx		
256Mb	8M x 32	AS4C8M32S-7BCN		MT48LC8M32B2B5-x	HY5V52CF	IS42S32800G-xBL	W9825G2JB-x		EM63A325BM		EDS2532EEBH
512Mb	32M x 16	AS4C32M16SA-7TCN	K4S511632M-TC75	MT48LC32M16A2P-75		IS42S16320B					

DDR1 DRAM



DENSITY	ORG	VCC	PACKAGE	SPEED (MHz)	TEMPERATURE	ALLIANCE
64Mb	4M x 16	2.5V	66pin TSOP II	200 MHz	Commercial, Industrial	AS4C4M16D1-5TCN/5TIN
128Mb	8M x 16	2.5V	66pin TSOP II, 60-ball FBGA	200 MHz	Commercial, Industrial	AS4C8M16D1-5TxN/5BxN
256Mb	16M x 16	2.5V	66pin TSOP II, 60-ball FBGA	200 MHz	Commercial, Industrial	AS4C16M16D1-5TxN/5BxN
512Mb	32M x 16	2.5V	66pin TSOP II, 60-ball FBGA	200 MHz	Commercial, Industrial	AS4C32M16D1-5TxN/5BxN

DDR1 DRAM Cross Reference

DENSITY	ALLIANCE	SAMSUNG	MICRON	ISSI	HYNIX	WINBOND	NANYA	ELPIDA	ETRON
64Mb	AS4C4M16D1-5TCN								EM6A8160TSA
128Mb	AS4C8M16D1-5TCN/5Bxx	K4H281638D			HY5DU1281622	W9712G6KB			EM6A9160TSA
256Mb	AS4C16M16D1-5TCN/5Bxx	K4H561638D	MT46V16M16	IS43R16160B	HY5DU561622	W9425G8EH	NT5DS16M16	EDD2516	EM6AA160TSC
512Mb	AS4C32M16D1-5TCN/5Bxx	K4H511638D	MT46V32M16	IS43R16320D	HY5DU121622		NT5DS32M16	EDD5116	EM6AB160TSE

DDR2 DRAM

DENSITY	ORG	VCC	PACKAGE	SPEED (MHz)	TEMPERATURE	ALLIANCE
512Mb	32M x 16	1.8V	84-ball FBGA	400 MHz	Commercial, Industrial	AS4C32M16D2-25BCN/25BIN
1G	64M x 16	1.8V	84-ball FBGA	400 MHz	Commercial, Industrial, Automotive	AS4C64M16D2-25BCN/25BIN/25BAN
1G	128M x 8	1.8V	60-ball FBGA	400 MHz	Commercial, Industrial	AS4C128M8D2-25BCN/25BIN
2G	128M x 16	1.8V	84-ball FBGA	400 MHz	Commercial, Industrial	AS4C128M16D2-25BCN/25BxN

DDR2 DRAM Cross Reference

DENSITY	ALLIANCE	SAMSUNG	MICRON	ISSI	WINBOND	NANYA	ELPIDA	ETRON	HYNIX	PROMOS
512Mb	AS4C32M16D2-25BCN	K4T51163Q	MT47H32M16HR-25E	IS43DR16320B	W975196KB	NT5TU32M16D9		EM68B16CWQD	H5PS5162FFR	
1G	AS4C64M16D2-25BCN	K4T1G164QF-BI	MT47H64M16H-25IT	IS43DR16640A	W971GG6JB		EDE1116	EM68C16WQD-xx	H5PS1G63JFR	
1G	AS4C128M8D2-25BCN	K4T1G084QF-BI	MT47H128M8H-25	IS43DR128804A	W971GG8JB		EDE1108	EM68C08CWAA-xx	H5PS1G83EFR	
2G	AS4C128M16D2-25xxx		MT47H128M16RT	IS43DR1628	W972GG6JB					V59C1G02168QCP25

MOBILE DDR

DENSITY	ORG	VCC	PACKAGE	SPEED (MHz)	TEMPERATURE	ALLIANCE
256Mb	x16	1.8V	60-ball FPBGA	166 MHz	Extended	AS4C16M16MD1-6BCN
512Mb	x16	1.8v	60-ball FPBGA	166 MHz	Extended	AS4C32M16MD1-6BCN
1G	x16	1.8V	60-ball FPBGA	166 MHz	Commercial, Industrial	AS4C64M16D1-6BxN

MOBILE DDR Cross Reference

DENSITY	ALLIANCE	MICRON	SAMSUNG	ISSI	HYNIX	NANYA	PROMOS
256Mb	AS4C16M16MD1-6BCN	MT46H16M16LFBF-5	K4X5616SPN-FG6		H5M525625FR	NT6DM16M16AD-TI	
512Mb	AS4C32M16MD1-6BCN	MT46H32M16LFBF-5	K4X511632PN-FG6			NT6DM32M16AD-TI	
1G	AS4C64M16MD1-6xxx	MT46H64M16LFBF		IS43LR16640A			V561G01164MCJ6

DDR3 DRAM



DENSITY	ORG	VCC	PACKAGE	SPEED (MHz)	TEMPERATURE	ALLIANCE
1G	x16	1.5V	96-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C64M16D3-12BxN
1G	x8	1.5V	78-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C128M8D3-12BxN
2G	x16	1.5V	96-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C128M16D3-12BxN
2G	x8	1.5V	78-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C256M8D3-12BxN
4G	x16	1.5V	96-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C256M16D3-12BxN
4G	x8	1.5V	78-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C512M8D3-12BxN
1G	x16	1.35V	96-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C64M16D3L-12BxN
1G	x8	1.35V	78-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C128M8D3L-12BxN
2G	x16	1.35V	96-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C128M16D3L-12BxN
2G	x8	1.35V	78-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C256M8D3L-12BxN
4G	x16	1.35V	96-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C256M16D3L-12BxN
4G	x8	1.35V	78-ball FBGA	800 MHz	Commercial, Industrial, Automotive	AS4C512M8D3L-12BxN

DDR3 DRAM Cross Reference

DENSITY	ALLIANCE	MICRON	SAMSUNG	ISSI	HYNIX	WINBOND	ELITE (ESMT)	ELPIDA	NANYA	ETRON
1G	AS4C64M16D3-12BxN	MT41J64M16JT-15E	K4B1G1646G-BCF	IS43TR16640A-xBL	H5TQ1G63DFR-x	W631GG6KB-x	M15F1G1664A-ADBG	EDJ1116DJBG	NT5CB64M16FP-DH	EM6GC16EWXA-xxH
1G	AS4C64M16D3L-12BxN	MT41K64M16JT-15E	K4B1G1646G-BYF	IS43TR16640AL-xBL	H5TC1G63DFR-x	W631GU6KB-x		EDJ1116EJBG	NT5CC64M16FP-DH	EM6HC16EWXD-xxH
1G	AS4C128M8D3-12BxN	MT41J128M8JP-15E	K4B1G0864G-BCF	IS43TR81280A-xBL	H5TQ1G83DFR-x	W631GG8KB-x		EDJ1108DJBG	NT5CB128M8FN-DH	EM6GC08EWUA-xxH
1G	AS4C128M8D3L-12BxN		K4B1G0864G-BYF	IS43TR81280AL-xBL	H5TC1G83DFR-x	W631GU8KB-x		EDJ1108EJBG	NT5CC128M8FN-DH	EM6GC08EXUA-xx
2G	AS4C128M16D3-12BxN	MT41J128M16HA-15E		IS43TR16128A-xBL	H5TQ2G63BFR-x	W632GG6KB-x	M15F2G16128A-ADBG	EDJ2116DEBG	NT5CB128M16HP-EK	EM6GD16EWXA-xxH
2G	AS4C128M16D3L-12BxN			IS43TR16128AL-xBL	H5TC2G63FFR-x	W632GU6KB-x		EDJ2116EEBG	NT5CC128M16HP-EK	EM6GH16EWXA-xxH
2G	AS4C256M8D3-12BxN	MT41J256M8HX-15E	K4B2G0846E-BCF	IS43TR82560A-xBL	H5TQ2G83EFR-x	W632GG8KB-x		EDJ2108DEBG	NT5CB256M8FN-FL	EM6GD08EWUX-xx
2G	AS4C256M8D3L-12BxN		K4B2G0846E-BYF	IS43TR82560AL-xBL	H5TC2G83EFR-x	W632GU8KB-x		EDJ2108EEBG	NT5CC256M8FN-FL	EM6GD08EWXC-xx
4G	AS4C256M16D3-12BxN	MT41J256M16RE-15E	K4B4G1646B-BCF	IS43TR16256A-xBL	H5TQ4G63AFR-x			EDJ4216BFBG	NT5CB256M16CP-FL	EM6GE16EW5B-xxH
4G	AS4C256M16D3L-12BxN	MT41K256M16RE-15E	K4B4G1646B-BYF	IS43TR16256AL-xBL	H5TC4G63AFR-x			EDJ4216EFBG	NT5CC256M16CP-FL	EM6HE16EWXC-xx
4G	AS4C512M8D3-12BxN	MT41J512M8RA-15E	K4B4G0846D-BCF	IS43TR85120A-xBL	H5TQ4G83AFR-x			EDJ4208BFBG	NT5CB512M8CN-FL	EM6GE08EW8C-xx
4G	AS4C512M8D3L-12BxN	MT41K512M8RA-15E	K4B4G0846D-BYF	IS43TR85120AL-xBL	H5TQ4G83AFR-x			EDJ4208EFBG	NT5CC512M8CN-FL	EM6GE08EWXC-xx

Alliance Packaging Quantities



FAST SRAM ORDER QTY

Part #	Package Suffix	Package	Box Qty	Quantity Per Tray/Tube	Reel size	Tape Width (mm)	Tape Pitch (mm)
164A, 256A, 3256A	JxN	28 SOJ - 300mil	2500	25/tube	1000	24	12
256B	JIN	28 SOJ - 300mil	1080	27/tube	1000	24	12
3256B	JIN	28 SOJ - 300mil	1352	26/tube	1000	24	12
256A, 3256A	TxN	28 TSOP I (8x13.4)	2340	234/tray	1000	24	12
1025B, 31025B, 1024B, 31024B	TJCN	32.3 SOJ - 300mil	2200	22/tube	1000	32	12
1024C	TJIN	32.3 SOJ - 300mil	920	23/tube	1000	32	12
31025C	TJIN	32.3 SOJ - 300mil	805	23/tube	1000	32	12
1025B, 31025B, 1024B, 31024B	JCN	32.4 SOJ - 400mil	2100	21/tube	1000	32	16
1024C, 1025C, 31025C	JIN	32.4 SOJ - 400mil	805	23/tube	1000	32	16
513B, 3513B, 1026B, 31026B	JCN	44 SOJ - 400mil - 1 Meg	1600	16/tube	500	44	16
1026C, 31026C	JIN	44 SOJ - 400mil - 1 Meg	560	16/tube	500	44	16
1024B, 31024B	TCN	32 TSOP I (8x20)	1560	156/tray	1000	32	12
31025C	TIN	32 TSOP I (8x20)	805	23/tube	1000	32	12
513B, 3513B, 1026B, 31026B	TCN	44 TSOP II - 400mil - 1 Meg	1350	135/tray	1000	32	16
1026C, 31026C	TIN	44 TSOP II - 400mil - 1 Meg	1352	26/tube	1000	32	16
4096A, 34096A, 4098A, 34098A	TxN	44 TSOP II - 400mil - 4 Meg	1350	135/tray	1000	32	16
4096A, 34096A	JxN	36 SOJ - 400mil	1900	19/tube	500	44	16
4098A, 34098A	JxN	44 SOJ - 400mil - 4 Meg	1600	16/tube	500	44	16
34098A	B	48ball BGA	2200	480/tray			
38096A, 38098A	TIN	44 TSOP II	1350	135/tray	1000	44	16
38096A, 38098A	B	48ball BGA	4800	480/tray	2000	44	16
316096A, 316098A	TIN	48 TSOP I	1350	135/tray	1000	44	16
316098A	B	48ball BGA	4800	480/tray	2000	16	16


LOW POWER SRAM ORDER QTY

Part #	Package Suffix	Package	Box Qty	Quantity Per Tray/Tube	Reel size	Tape Width (mm)	Tape Pitch (mm)
6264/62256	S	28pin 330mil SOP	2500	25/tube	1000	24	16
6264/62256	P	28pin 600mil DIP	600	15s/tube	NA	NA	NA
6264/62256	ST	28pin STSOP (8x13.4)	2340	234/tray	1500	24	12
1008/2008/4008	P	32pin 600mil DIP	520	13s/tube	NA	NA	NA
1008/2008/4008	S	32pin 450mil SOP	2200	22/tube	1000	32	16
1008/2008/4008	T	32pin TSOP I (8x20)	1560	156/tray	1500	32	12
1008/2008/4008	ST	32pin STSOP (8x13.4)	2340	234/tray	1500	24	12
1016/2016/4016/8008/8016	Z	44pin TSOP II 400mil	1350	135/tray	1000	32	12
1616	T	48pin TSOP I	960	96/tray	1000		
1008/2008/4008/8008/1016/1616/2016/4016/8016/1616/3216	B	36B/48B TFBGA (6x8)	4800	480/tray	2000	16	12
4008	Z	32pin TSOP II	1170	117/tray	1000	32	16

DRAM ORDER QTY

Part #	Package	Box Qty	Quantity Tray/Reel	Reel size
AS4C1M16S	50pin TSOP II	1170	117/Tray	1000
AS4C4M16S	54pin TSOP	1080	108/Tray	1000
AS4C8M16S	54pin TSOP	1080	108/Tray	1000
AS4C16M16S	54pin TSOP	1080	108/Tray	1000
AS4C8M16S	54ball BGA	3480	348/Tray	1000
AS4C16M16S	54ball BGA	3480	348/Tray	1000
AS4C2M32S	86pin TSOP	1080	108/Tray	1000
AS4C4M32S	86pin TSOP	1080	108/Tray	1000
AS4C2M32S	90ball BGA	1900	190/Tray	1000
AS4C4M32S	90ball BGA	1900	190/Tray	1000
AS4C8M32S	90ball BGA	1900	190/Tray	1000
AS4C4M16D1	66pin TSOP	1080	108/Tray	1000
AS4C8M16D1	66pin TSOP	1080	108/Tray	1000
AS4C16M16D1	66pin TSOP	1080	108/Tray	1000
AS4C32M16D1	66pin TSOP	1080	108/Tray	1000
AS4C32M16D2	80ball FBGA	3480	348/Tray	1000
AS4C64M16D2	80ball FBGA	2090	209/Tray	1000
AS4C128M8D2	60ball FBGA	2090	209/Tray	1000
AS4C128M8D3	78ball FBGA	2420	242/Tray	1000
AS4C64M16D3	96ball FBGA	1900	190/Tray	1000
AS4C128M16D3	96ball FBGA	1900	190/Tray	1000
AS4C256M8D3	78ball FBGA	2420	242/Tray	1000
AS4C256M16D3	96ball FBGA	1900	190/Tray	1000
AS4C512M8D3	78ball FBGA	2200	220/Tray	1000
AS4C16M16MD1	60ball FBGA	3480	348/Tray	1000
AS4C32M16MD1	60ball FBGA	3480	348/Tray	1000

ALLIANCE PART NUMBERING SYSTEM



MAIN OFFICES

US Headquarters

Alliance Memory, Inc.
511 Taylor Way
San Carlos, CA 94070
Phone: (650) 610-6800
Fax: (650) 620-9211

EMEA Headquarters

Alliance Memory, Inc.
20 Grensell Close
Eversley, Hampshire RG27 0QQ
United Kingdom
Phone: +44 (0)787 634 4055

Asia Headquarters

Alliance Memory, Inc.
9F., No.93, Aly. 3, Ln. 182, Sec. 2, Wenhua Rd.
Banqiao Dist., New Taipei City
Taiwan 22047
Phone: +[886] 0922176476

China Headquarters

Room 301, No. 2, 6th Alley,
TangYan, Shangsha, Futian District
Shenzhen, Guangdong
China 518048
Phone: +[86] 18926006867

Hong Kong Sales Office

Unit 601, Block D,
Amoy Garden, Ngau Tau Kok
Kowloon, Hong Kong
Phone: +852-9271-6282 or +86-136-0267-1021

Japan Sales Office

3-7-10, Sakurajyousui, Setagaya-Ku
Tokyo, Japan 156-0045
Phone: +81-90-3963-0869

France Sales Office

Alliance Memory, Inc.
BP 517
13001 Marseille France
Phone: +33 (0) 670 00 37 22

Sweden Sales Office

Högvägen 2
SE-131 42 NACKA, Sweden
Phone: +46 8 716 88 78
Mobile: +46 70 130 36 21

Italy Sales Office

Via Edison 14/16
20090 Segrate (Milano) Italy
Phone: +39 02 2134 408
Fax: +39 02 2692 7410

NORTH AMERICA REP

CUSTOMER 1ST

MN, IA, KS, ND, SD, MO
2950 Metro Drive, Suite 101
Bloomington, MN 55425
Phone: (952) 851-7909
Fax: (952) 851-7907

TRISTAR GROUP

Texas, Oklahoma, Louisiana, Mexico
5220 Spring Valley Road #190
Dallas, Texas 75254
Phone: (972) 392-2848
Fax: (972) 329-3861

CRESTONE TECHNOLOGY GROUP

Colorado, Utah, Idaho, Montana
7108 South Alton Way, Bldg. L
Centennial, CO 80112
Phone: (303) 280-7202
Fax: (720) 482-2220

SOUTH AMERICA REP

MASTERTRONICS

All of Brazil
Rua Gen. João Telles, 542 cj 704
Porto Alegre - RS - Brasil - 90035 120
Phone: +55 51 3312-6757
Fax: +55 51 3312-6758

**For a complete list of our distributors
and REP Partners by country and
region, please refer to our web site,
www.alliancememory.com**



ONLINE TECH SUPPORT

www.alliancememory.com/products/techsupport.htm

ONLINE STORE-BUY DIRECT

www.alliancememory.com/products/buynow.htm

SALES

sales@alliancememory.com



facebook.com/pages/Alliance-Memory-Inc



[@alliancememory](https://twitter.com/alliancememory)

