


SERIES**MILS1812R
MILS1812****Shielded Surface Mount Inductors**

Actual Size

**Military QPL Approvals**

M83446/40

* Suffix F: Tin/Lead Termination

* Suffix P: Tin Termination

Physical Parameters

	Inches	Millimeters
A	0.166 to 0.190	4.2 to 4.8
B	0.118 to 0.134	3.0 to 3.4
C	0.118 to 0.134	3.0 to 3.4
D	0.015 Min.	0.38 Min.
E	0.054 to 0.078	1.37 to 1.98
F	0.118 (Ref. only)	3.0 (Ref. only)
G	0.066 (Ref. only)	1.7 (Ref. only)

Dimensions "A" and "C" are over terminals


Weight Max. (Grams) 0.15**Operating Temperature Range** -55°C to +125°C**Current Rating at 90°C Ambient** 35°C Rise**Maximum Power Dissipation at 90°C** 0.278 W

**†Note Self Resonant Frequency (SRF) values are calculated and for reference only.

Marking API/SMD; inductance with units and tolerance followed by an S; date code (YYWWL) followed by an M. Note: An R before the date code indicates a RoHS component.

Example: MILS1812-153K

API/SMD
15uH±10%S
0850A M

Made In the U.S.A.

For more detailed graphs, contact factory

M83446/40 IRON CORE							
INDUCTANCE (μH) ±10%	MIL DASH #	TEST FREQUENCY (MHz)	Q MINIMUM	SRF MINIMUM (MHz)	DC RESISTANCE MAXIMUM (OHMS)	CURRENT RATING MAXIMUM (mA)	
-101K	-01*	0.10	50	25	460**†	0.09	1490
-121K	-02*	0.12	50	25	400**†	0.10	1412
-151K	-03*	0.15	50	25	390**†	0.11	1347
-181K	-04*	0.18	50	25	350**†	0.12	1290
-221K	-05*	0.22	50	25	310**†	0.15	1154
-271K	-06*	0.27	50	25	280**†	0.18	1053
-331K	-07*	0.33	40	25	240	0.22	952
-391K	-08*	0.39	40	25	215	0.26	876
-471K	-09*	0.47	40	25	205	0.31	802
-561K	-10*	0.56	40	25	185	0.37	735
-681K	-11*	0.68	40	25	166	0.44	675
-821K	-12*	0.82	40	25	155	0.53	614
M83446/40 FERRITE CORE							
-102K	-13*	1.0	40	7.9	160	0.35	755
-122K	-14*	1.2	40	7.9	140	0.38	725
-152K	-15*	1.5	40	7.9	110	0.40	706
-182K	-16*	1.8	40	7.9	100	0.43	681
-222K	-17*	2.2	40	7.9	90	0.46	658
-272K	-18*	2.7	40	7.9	67	0.49	638
-332K	-19*	3.3	40	7.9	61	0.70	534
-392K	-20*	3.9	40	7.9	56	0.84	487
-472K	-21*	4.7	40	7.9	50	0.90	471
-562K	-22*	5.6	40	7.9	40	1.00	447
-682K	-23*	6.8	40	7.9	32	1.20	408
-822K	-24*	8.2	40	7.9	30	1.44	372
-103K	-25*	10	50	2.5	25	1.80	333
-123K	-26*	12	50	2.5	22	2.00	315
-153K	-27*	15	50	2.5	18	2.20	301
-183K	-28*	18	50	2.5	15	2.40	288
-223K	-29*	22	50	2.5	14	2.60	277
-273K	-30*	27	50	2.5	13	2.80	267
-333K	-31*	33	50	2.5	12	3.00	258
-393K	-32*	39	50	2.5	11	3.20	250
-473K	-33*	47	50	2.5	9.0	3.40	242
-563K	-34*	56	50	2.5	8.0	3.60	235
-683K	-35*	68	50	2.5	7.6	4.30	215
-823K	-36*	82	50	2.5	7.2	5.20	196
-104K	-37*	100	40	0.79	7.0	7.00	169
-124K	-38*	120	40	0.79	6.0	7.50	163
-154K	-39*	150	40	0.79	5.0	8.00	158
-184K	-40*	180	40	0.79	4.5	8.50	153
-224K	-41*	220	40	0.79	4.2	9.00	149
-274K	-42*	270	40	0.79	4.0	11.0	135
-334K	-43*	330	40	0.79	3.7	12.0	129
-394K	-44*	390	40	0.79	3.5	18.0	105
-474K	-45*	470	40	0.79	3.3	24.0	91
-564K	-46*	560	40	0.79	2.8	28.0	84
-684K	-47*	680	40	0.79	2.6	32.0	79
-824K	-48*	820	40	0.79	2.2	40.0	71
-105K	-49*	1000	40	0.79	2.0	55.0	60

Parts listed above are QPL/MIL qualified

*Complete part # must include series # PLUS the dash #

For surface finish information,
refer to www.delevanfinishes.com

Packaging Tape & reel (12mm): 7" reel, 650 pieces max.; 13" reel, 2500 pieces max.

*** Termination Finish Options** (Part & Callout)

MILS1812 - 101K = M83446/30F (Tin/Lead)

MILS1812R - 101K = M83446/13P (Pb free)