

6

5


4

3



2

1


MATERIAL NUMBER	OLD PART NUMBER
120091-0004	N03MA03124
120091-0010	N04MA03124



3 POLE FACE VIEW



4 POLE FACE VIEW



VOLTAGE RATING	60 VAC/ 75VDC
AMPERAGE RATING	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	0°C TO 80°C

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PA	BLACK
2	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
3	COUPLING NUT	BRASS	NICKEL PLATED
4	HOUSING	PA	BLACK
5	CORD GRIP	PA	BLACK

EC NO: WNA2010-0139 DRWN: BWOODMAN 8/26/09 CHKD: JFJ APPR: JFMURPHY 2009/08/31	QUALITY SYMBOLS ▽=0 ▽C=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS ----	THIRD ANGLE PROJECTION ☉			
				mm	INCH	DRAWN BY BW	DATE 2009/04/03	TITLE M8 MALE ATTACHABLE 3P SOLDER ----				
			4 PLACES	±----	±---	CHECKED BY TW	DATE 2009/04/03					
			3 PLACES	±----	±---	APPROVED BY JFMURPHY		DATE 2009/08/28	MOLEX INCORPORATED molex			
C	REV		2 PLACES		±----	±.01	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-120091-001		SHEET NO. 1 OF 1	
			1 PLACE		±0.3	±---	SIZE A		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
					ANGULAR ±----°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					