

General ordering data

Order No.	0128370000
Part designation	SAK 4 KRG BL
Version	Feed-through terminal, 4 mm ² , Screw connection, KrG, blue, TS 32
EAN	4008190110475
Qty.	100 pc(s).

Product notes

Note, technical data	With twin ferrules ZH 0.5 to ZH 2.5, rated voltage is 690 V.
----------------------	--

PT OKIECEx/ATEX rating data

EU-type examination certificate	KEMA97ATEX1798U
Download, German	KEMA97ATEX1798U_d.pdf
Download English	KEMA97ATEX1798U_e.pdf
IECEx Certificate of Conformity	IECExKEM06.0014U
ATEX voltage	550 V
ATEX current	28 A
ATEX conductor cross-section	4 mm ²
IECEx voltage	550 V
IECEx current	28 A
IECEx conductor cross-section	4 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEx-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	blue
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 32
Insulating material	KrG
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 60 °C, + 130 °C
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	5VA
Version	Feed-through terminal

CSA rating data

Voltage (CSA)	600 V
CSA current	36 A

CSA rating data

Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 10

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	4 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	2
Stripping length	12 mm
Clamping screw	M 3
Blade size	0.6 x 3.5 mm
Tightening torque range	0.5...1.0 Nm
Torque level with DMS electric screwdriver	2
Gauge to IEC 60947-1	A4
Solid, min.	0.5 mm ²
Solid, max.	6 mm ²
Stranded, min.	0.5 mm ²
Stranded, max.	4 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	4 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	4 mm ²
Twin wire-end ferrule, min.	0.5 mm ²
Twin wire end ferrule, max.	2.5 mm ²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 10
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	5.26 mm ²

Dimensions

Width	6.5 mm
Height of lowest version	51.5 mm
Length	40 mm
Weight	14.37 g
TS 32 offset	20 mm

Disconnect terminals

Torque level with DMS electric screwdriver	2
--	---

Rating data

Rated cross-section	4 mm ²
Rated voltage	800 V
Rated impulse voltage	8 kV
Rated current	32 A
Standards	IEC 60947-7-1
Current with max. conductor	41 A
Pollution severity	3

UL rating data

Voltage (UL)	600 V
Current (UL)	20 A
Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 12

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000897
ETIM 3.0	EC000897
eClass 4.1	27-14-11-20
eClass 5.0	27-14-11-20
eClass 5.1	27-14-11-20

Similar products

Order No.	Part designation	Version
0128320000	SAK 4 KRG	Feed-through terminal, 4 mm ² , Screw connection, KrG, Medium yellow, TS 32