






- D
1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED FOR AUTOMATIC INSERTION.
3. BECU CONTACT-PLATED WITH TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. PHOS. BRONZE CONTACT- PLATED WITH TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
5. MAXIMUM DIMENSION FOR I.C. SEATING PLANE.
6. HOUSING MATERIAL-GLASS FILLED THERMOPLASTIC, BLACK, 94V-0
7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- C



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4:1

OBSOLETE 7	3	.900	9	.995	20	1-1825373-6
	5	.800	8	.895	18	1-1825373-5
	3	.700	7	.795	16	1-1825373-4
	3	.600	6	.695	14	1-1825373-3
	3	.300	3	.395	8	1-1825373-2
OBSOLETE 4	3	.200	2	.295	6	1-1825373-1
	4	.900	9	.995	20	1825373-6
	4	.800	8	.895	18	1825373-5
	4	.700	7	.795	16	1825373-4
	4	.600	6	.695	14	1825373-3
OBSOLETE 4	4	.300	3	.395	8	1825373-2
	4	.200	2	.295	6	1825373-1

CONTACT & FINISH		DIM C	B SPCS	DIM A	POSITION	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	29DEC2005	Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: INCHES		CHK D ROHDE	29DEC2005	NAME DIP SOCKET ASSY, CLOSED, DIPLOMATE, RETENTIVE LEAD, .300 CL, LEAD FREE		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D D ROHDE	29DEC2005	PRODUCT SPEC		
0 PLC ± -		APPLICATION SPEC		SIZE A1		
1 PLC ± -		WEIGHT		CAGE CODE 00779		
2 PLC ± -		CUSTOMER DRAWING		SCALE 5:1		
3 PLC ± -		SHEET 1		OF 1		
4 PLC ± -		REV A1		RESTRICTED TO		
ANGLES ± -		MATERIAL		DRAWING NO 1825373		
FINISH		MATERIAL		DRAWING NO 1825373		