



Product Search:

3721...ç•µ•û£...£µç×•


[About Us](#) | [Products](#) | [Contact Us](#) | [Culture](#) | [Web Manage](#)

[中文版](#)

[Home](#)


Location: Product Search

3.0 AMPERES /SMC(D0-214AB)



TYPE	Maximum Peak Reverse Voltage PRV V _{PK}	Maximum Average Rectified Current @Half-wave Resistive Load 60Hz I _O @ T _A A _{AV}	Maximum Average Rectified Current @Half-wave Resistive Load 60Hz I _O @ T _A °C	Maximum Forward Peak Surge Current @8.3ms Superimposed I _{FM} (Surge) A _{PK}	Maximum Reverse Current @PRV @25°C T _A I _R •Adc	Maximum Forward Voltage @25•• T _A I _{FM} A _{PK}	Maximum Forward Voltage @25•• T _A V _{FM} V _{PK}	
S3A	50	3.0	75	100	10	3.0	1.2	
S3B	100	3.0	75	100	10	3.0	1.2	
S3D	200	3.0	75	100	10	3.0	1.2	
S3G	400	3.0	75	100	10	3.0	1.2	
S3J	600	3.0	75	100	10	3.0	1.2	
S3K	800	3.0	75	100	10	3.0	1.2	
S3M	1000	3.0	75	100	10	3.0	1.2	

OPERATIONG AND STORAGE TEMPERATURE -65°C TO +175°C



Copyright 2003 Changzhou Star Sea Electronics Co.,Ltd. All right Reserved.
Add: 18 Sanjing Road West, Changzhou, Jiangsu, China
Tel: +86-519-5111018 5111098 Fax: +86-519-5112846 5122846
E-mail: starsea@public.cz.js.cn P.C.: 213022