



TR300

Temperature and Relative Humidity Data Logger

The Amprobe TR300 temperature and humidity data logger is designed to monitor indoor air quality in one compact size unit. The housing includes a wall-mount hook for easy installation. It has a large digital triple display and audible and visible alarms. Plus a fast responding sensor and electronics to help monitor the relative humidity and temperature of the indoor air.

The TR300 has capacity to store 16,000 readings and ships with the unique Amprobe Download Suite software. Set up these parameters for recording: Sample interval timing, Start/Stop, Date and Time, HI/LO Alarm threshold, Unit Selection and number of Memory points. Download Suite software works with all Amprobe devices and stores the data from the TR300 for further analysis.

No hassle warranty

No waiting.

No shipping charges.



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSRP limit)

- Instrument for indoor air quality monitoring
- Temperature / RH in one model
- Wall mountable, self-standing or tripod mountable
- Extra large digital display
- Displays Temperature, RH plus Real time date/hour stamp
- Air Temperature or Dew Point (DP) display and Celsius/ Fahrenheit are selectable
- Offers both visible LEDs plus audible warnings to monitor IAQ condition
- Small size design with USB interface
- Memory points selection : 1000, 2000, 4000, 6000, 8000,12000,16000
- Includes USB Cable, Amprobe's Download Suite Software CD, Table Feet, User Manual, Batteries



TR300 Temperature and Relative Humidity Data Logger

Data Sheet

Specifications

General		
Range	Relative Humidity Temperature	0 to 100% -20 to 70°C (-4 to 158°F)
Accuracy	Relative Humidity Temperature	±3% @ 10~90%; ±5% @ others ±0.6°C (±1°F) @ 0~50°C (32°F~122°F); ±1.2°C (±2°F) @ others
Resolution	Temperature Humidity	0.1°C/ 0.1°F 0.1%
Battery Life	150 Hours	
Electrical		
Battery	4 ea AA batteries included	
Mechanical		
Dimension	175 x 42 x 16 mm (6.89 x 1.65 x 0.63 in)	
Weight	0.282 Kg (0.622 lb)	
Case	N/A	
Environmental		
Operating Humidity	0-100% RH	
Operating Temperature	-20 to 70°C (-4 to 158°F)	
Storage Temperature	-20 to 70°C (-4 to 158°F)	
Agency Approvals & Certifications	CE	

Amprobe® Test Tools
website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

Amprobe® Test Tools Europe
Amprobe Test Tools Europe
Beha-Amprobe GmbH
In den Engematten 14
79286 Glottertal, Germany
Tel.: +49 (0) 7684 8009 - 0

©2008 Amprobe Test Tools. All rights reserved.
7/2008 3358086 Rev A