



Datasheet for part number DCMN37SNA197

|                                                                       |
|-----------------------------------------------------------------------|
| Our Catalog Part Number: DCMN-37S-N-A197                              |
| Our Global Manufacturing Part Number: 053514-3466                     |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M |

| Product Datasheet               |                                                   |
|---------------------------------|---------------------------------------------------|
| General                         | D*M High reliable D-Sub Connectors                |
| Wire Gauge Range AWG            | AWG 20-28                                         |
| Mating Cycles                   | 200                                               |
| Contact Arrangement             | 37 contacts size 20                               |
| Dielectric Withstanding Voltage | 1000 VAC at sea level                             |
| Current Rating                  | 7.5 A max                                         |
| Contact Resistance              | 7.5 milli Ohm max                                 |
| Operating Temperature           | -55°/+125°                                        |
| Salt Spray Test                 | 20 hours                                          |
| Shell Material                  | steel                                             |
| Shell Finish                    | pur tin over nickel                               |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                  |
| Insulator Color                 | black                                             |
| Gender                          | Socket                                            |
| Contact Type                    | Straight PCB                                      |
| Contact Material                | copper alloy                                      |
| Contact Finish                  | gold over nickel                                  |
| Hardware                        | .300? (7.6mm) Standoff, 4-40 Screwlock, Boardlock |