



MATERIALS:

Body and Fittings: Brass, Tarnish Resistant Plating.

Center Contact: Brass, Gold Plated.

Dielectric: Teflon

Gasket: Silicone rubber

Resistor: Deposited carbon film

Marking: "Pomona 4240"

Label: "TERM, *Ω 1W"

RATINGS:

Frequency Range: DC to 500 MHz

Resistance Tolerance: $\pm 1\%$

Power: 1W @ 70°C Max.

ORDERING INFORMATION: Model 4240-*

*= Resistance Value 50, 75, 600

Ordering Example: 4240-50 = 50 Ohm Value Resistance

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4240-75](#)