

Heavy Duty AC Rated Toggle Switches

General Purpose switches rated at 15 amps, 125 VAC and 28 VDC and 10 amps at 250 VAC. UL listed and CSA certified in single, double, three and four pole configurations. All are rated 3/4 H.P. — 15/32" bushing — 11/16" Toggle.

Stock No.	Mfr.'s Type	Switch Action	Terminals	EACH			
				1-24	25-99	100-499	500-999
683-0048 683-0049	2FA53-73 2FA53-73-TABS	S.P.S.T. ON-NONE-OFF S.P.S.T. ON-NONE-OFF	Solder Spade	3.59 3.59	2.77 2.77	2.43 2.43	2.13 2.13
683-0050 683-0051 683-0052	2FA54-73 2FB53-73 2FB53-73-TABS	S.P.S.T. ON-NONE-OFF S.P.D.T. ON-NONE-ON S.P.D.T. ON-NONE-ON	Screw Solder Spade	4.11 4.41 4.41	3.18 3.43 3.43	2.79 3.01 3.01	2.79 2.64 2.64
683-0053 683-0054	2FB54-73 2FC53-73	S.P.D.T. ON-NONE-ON S.P.D.T. ON-OFF-ON	Screw Solder	5.19 4.41	4.02 3.43	3.53 3.01	3.09 2.64
683-0055 683-0056 683-0057	2FC53-73-TABS 2FC54-73 6FC54-73*	S.P.D.T. ON-OFF-ON S.P.D.T. ON-OFF-ON S.P.D.T. ON-OFF-ON	Spade Screw Screw	4.41 5.19 7.22	3.43 4.02 5.59	3.01 3.53 4.90	2.64 3.09 4.30
683-0058 683-0059	2GK50-73 2GK51-73	D.P.S.T. ON-NONE-OFF D.P.S.T. ON-NONE-OFF	Solder Spade	5.68 5.68	4.41 4.41	3.87 3.87	3.39 3.39
683-0060 683-0061 683-0062	2GK54-73 2GL50-73 2GL51-73	D.P.S.T. ON-NONE-OFF D.P.D.T. ON-NONE-ON D.P.D.T. ON-NONE-ON	Screw Solder Spade	6.73 6.79 6.79	5.22 5.26 5.26	4.58 4.62 4.62	4.02 4.05 4.05
683-0063 683-0064	2GL54-73 2GM50-73	D.P.D.T. ON-NONE-ON D.P.D.T. ON-OFF-ON	Screw Solder	8.34 6.79	6.47 5.26	5.67 4.62	4.97 4.05
683-0065 683-0066 683-0067	2GM51-73 2GM54-73 HK250-73	D.P.D.T. ON-OFF-ON D.P.D.T. ON-OFF-ON 3.P.S.T. ON-NONE-OFF	Spade Screw Solder	6.79 8.34 10.43	5.26 6.47 8.08	4.62 5.67 7.09	4.05 4.97 6.21
683-0068 683-0069	HK251-73 HK254-73	3.P.S.T. ON-NONE-OFF 3.P.S.T. ON-NONE-OFF	Spade Screw	10.43 12.34	8.08 9.57	7.09 8.39	6.21 7.36
683-0070 683-0071 683-0072	HL250-73 HL251-73 HL254-73	3.P.D.T. ON-NONE-ON 3.P.D.T. ON-NONE-ON 3.P.D.T. ON-NONE-ON	Solder Spade Screw	12.82 12.82 15.34	9.93 9.93 11.89	8.71 8.71 10.43	7.64 7.64 9.15
683-0073 683-0074	HM250-73 HM251-73	3.P.D.T. ON-OFF-ON 3.P.D.T. ON-OFF-ON	Solder Spade	12.82 12.82	9.93 9.93	8.71 8.71	7.64 7.64
683-0075 683-0076 683-0077	HM254-73 IK250-73 IK251-73	3.P.D.T. ON-OFF-ON 4.P.D.T. ON-NONE-OFF 4.P.S.T. ON-NONE-OFF	Screw Solder Spade	15.34 14.30 14.30	11.89 11.08 11.08	10.43 9.72 9.72	9.15 8.52 8.52
683-0078 683-0079	IK254-73 IL250-73	4.P.S.T. ON-NONE-OFF 4.P.D.T. ON-NONE-ON	Screw Solder	15.87 17.46	12.30 13.53	10.79 11.86	9.46 10.40
683-0080 683-0081 683-0082	IL251-73 IL254-73 IM250-73	4.P.D.T. ON-NONE-ON 4.P.D.T. ON-NONE-ON 4.P.D.T. ON-OFF-ON	Spade Screw Solder	17.46 20.99 17.46	13.53 16.28 13.53	11.86 14.28 11.86	10.40 12.52 10.40
683-0083 683-0084	IM251-73 IM254-73	4.P.D.T. ON-OFF-ON 4.P.D.T. ON-OFF-ON	Spade Screw	17.46 20.99	13.53 16.28	11.86 14.28	10.40 12.52

*Momentary on action.

Nylon Insulated Toggle Switches



Series D switches have self-cleaning wiping action contacts suitable for both power and low-level switching nylon flat or bat lever actuators and bushing/frame super structure for double insulated requirements. UL listed, CSA certified. Series rated at 10 amps 125 VAC, 5 amps 250 VAC, 1/2 H.P. 125-250 VAC, 10 amps 28 VDC.

Paddle Toggle Actuator

Stock No.	Mfr.'s Type	Switch Action	Terminals	EACH			
				1-24	25-99	100-499	500-999
683-0085 683-0086 683-0087 683-0088	DA100-PB-B DA105-PB-B DB100-PB-B DC100-PB-B	S.P.S.T. ON-NONE-OFF S.P.S.T. ON-NONE-OFF S.P.D.T. ON-NONE-ON S.P.D.T. ON-OFF-ON	Solder/Spade Wire Solder/Spade Solder/Spade	2.44 3.57 2.73 2.73	1.90 2.77 2.12 2.12	1.66 2.43 1.86 1.86	1.46 2.13 1.63 1.63

Bat Toggle Actuator

683-0089 683-0090	DA100-BB-B DA105-BB-B	S.P.S.T. ON-NONE-OFF S.P.S.T. ON-NONE-OFF	Solder/Spade Wire	2.44 3.57	1.90 2.77	1.66 2.43	1.46 2.13
----------------------	--------------------------	--	----------------------	--------------	--------------	--------------	--------------



General Purpose Pushbutton Switches

Slow make/slow break momentary AC only. Circuitry: On-none-off. UL listed and CSA certified (P26A-1D-RND and P26L-1D-RND not shown).

6 Amps 125 VAC — 3 Amp 250 VAC

Stock No.	Mfr.'s Type	Switch Action	Terminals	Cap	EACH			
					1-24	25-99	100-499	500-999
683-0093 683-0094 683-0095 683-0097	P26A-1D-RND P26L-1D-RND P27A-BL P27L-BL	S.P.N.O. S.P.N.C. S.P.N.O. S.P.N.C.	Solder Solder Solder Solder	Metal Metal Black Black	5.48 5.48 4.93 4.93	4.24 4.24 3.81 3.81	3.72 3.72 3.35 3.35	3.26 3.26 2.93 2.93

15 Amps 125 VAC — 10 Amps 250 VAC

683-0099 683-0100	170 172	S.P.N.C. S.P.N.O.	Screw Screw	Metal Metal	8.65 8.65	6.71 6.71	5.89 5.89	5.16 5.16
----------------------	------------	----------------------	----------------	----------------	--------------	--------------	--------------	--------------

Quick Make/Quick Break Maintained AC/DC; 6 Amps 125 VAC — 3 Amps 250 VAC

683-0101 683-0102	110-SP 111-16P	S.P.S.T. S.P.S.T.	Screw Wire	Metal Metal	7.81 7.81	6.06 6.06	5.31 5.31	4.66 4.66
----------------------	-------------------	----------------------	---------------	----------------	--------------	--------------	--------------	--------------