



FK22M

Pointed tip penetration probe



Copyright © 2007 Test Products International, Inc.

Application

General purpose light duty
penetration applications
requiring fast response

Range°F°C

-58° to 500°F
-50° to 250°C

Probe tip

21

Dimensions

Stem Length: 4" (101.6mm)
Diameter: .09/.06"
(2.4/1.6mm)
Lead Length: 39.4" (1M)

Insulation Material

PTFE