



JUNCTION BOX

Mini 25-L



Mini 25-L

Junction box

89 x 43 x 37 mm

Article number: 31090801

Junction box acc. DIN EN 60670 (VDE 0606), 10 entries, 2 floor entries, suitable for confined installation environments such as suspended ceilings and cable ducts, complete with perforation tool and blanking plug, with external fixing positions

grey, without terminals, for VDE approved single terminals



Technical data

Measures

Width:	89 mm
Length:	43 mm
Height:	37 mm

Material

Base:	Polyethylene
Cover:	Polypropylene

Certificates



Accessory

VST RR - Blanking plugs

HandyGrip VG 20 - Terminal strip

HandyGrip VG 21 - Terminal strip

HandyGrip VG 21 w - Terminal strip

HandyQuick SQ 32 - screwless terminal

HandyQuick SQ 52 - screwless terminal



JUNCTION BOX

Mini 25-L

Other attributes

Color:	grey
Rated cross section:	2,5 mm²
Tackable:	No
Rated insulation voltage AC:	400 V
Explosion safety:	none
Fire protection:	none
sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP55 - acc. EN 60529 / DIN VDE 0470-1
Weatherproof:	No
Equiquest:	None

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short Therm):	95%
Max. rel. humidity at 40° C:	50%