



Search Results

Evaluate

- FAQ's

How to Buy


- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 


 Text Search: 'FJEPGS9CBU-CY'

Your search criteria matched only one product, shown below

FJEPGS9CBU-CY



- TIA/EIA-604 FOCIS-6 compliant connectors
- Exceed TIA/EIA-568-B.3 requirements
- Insertion loss: 0.1dB average (multimode), 0.2dB average (singlemode)
- Return loss: >20dB (multimode), >40dB (singlemode)
- RJ45 small form factor duplex plug
- Non-optical disconnect maintains data transmission under tensile loads
- Each duplex plug includes housing, insert, two ferrule assemblies, two crimp sleeves, one boot for 3mm jacketed cable and two dust caps
- Fiber cable type: tight-buffered recommended
- Fiber cable size: accept 3.0mm jacketed cable or 1.6mm - 2.0mm jacketed cable (noted in part description)
- Ferrule type: 2.5mm zirconia ceramic (highest durability for repeated matings)
- Field polish termination -- Panduit® recommends anaerobic adhesive
- Use field polish termination kit (FJKITG)

▪ Part Number	FJEPGS9CBU-CY
▪ RoHS Compliancy Status	Compliant
▪ Note	FJEPGS9CBU-CY replaces FJEPGS9CBU-C
▪ Part Description	FJ® Singlemode Duplex Fiber Optic Plug for 3mm jacketed cable installation. 100/pk
▪ CE Compliant	No
▪ Pricing Description	Enhanced FJ Plug Singlemode for 3.0mm Jacketed Cable (100 pack)
▪ Min. Order UOM	PC
▪ Min. Order Qty.	100
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.