



General ordering data

Order No.	0373100000
Part designation	H4,0/9
Version	Wire-end ferrule, 4 mm ²
EAN	4008190164669
Qty.	500 pc(s).

Technical data

Length	9 mm
Width	2.8 mm
Height	2.8 mm

Product data

Conductor rated cross-section	4 mm ²
AWG	12
Total length (L1)	9 mm
Contact surface diameter (D1)	2.8 mm
Metal sleeve thickness (S1)	0.2 mm

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000005
ETIM 3.0	EC000005
eClass 4.1	27-06-07-01
eClass 5.0	27-40-02-01
eClass 5.1	27-40-02-01

Similar products

Order No.	Part designation	Version
9018910000	H0.25/5	Wire-end ferrule, 0.25 mm ²
0282600000	H0.5/6	Wire-end ferrule, 0.5 mm ²
9004050000	H0,5/10	Wire-end ferrule, 0.5 mm ²
0282700000	H0.75/6	Wire-end ferrule, 0.75 mm ²
0542500000	H0.75/10	Wire-end ferrule, 0.75 mm ²
0372600000	H1,0/6	Wire-end ferrule, 1 mm ²
0282800000	H1,0/10	Wire-end ferrule, 1 mm ²
0372700000	H1,5/7	Wire-end ferrule, 1.5 mm ²
0186500000	H1,5/10	Wire-end ferrule, 1.5 mm ²

9004060000	H1,5/12	Wire-end ferrule, 1.5 mm ²
9004070000	H1,5/18	Wire-end ferrule, 1.5 mm ²
0373000000	H2,5/7	Wire-end ferrule, 2.5 mm ²
9004080000	H2,5/10	Wire-end ferrule, 2.5 mm ²
0186100000	H2,5/12	Wire-end ferrule, 2.5 mm ²
9004090000	H2,5/18	Wire-end ferrule, 2.5 mm ²
0244100000	H4,0/12	Wire-end ferrule, 4 mm ²
9004100000	H4,0/15	Wire-end ferrule, 4 mm ²
9004110000	H4,0/18	Wire-end ferrule, 4 mm ²
9004120000	H6,0/10	Wire-end ferrule, 6 mm ²
0191900000	H6,0/12	Wire-end ferrule, 6 mm ²
0124700000	H6,0/15	Wire-end ferrule, 6 mm ²
9004130000	H6,0/18	Wire-end ferrule, 6 mm ²