


HARDWARE

ALLIGATOR CLIP



STANDARD ALLIGATOR CLIPS

PART NO.	FIG.	INSUL COLOR	CLIP MATERIAL	WIRE CONNECT	RATED Amps	INSULATORS SOLD SEPARATELY
790-7001	1	Uninsul	Steel	Solder	5	790-7025-XX*
790-7035-10	3	Black	Steel	Screw	5	-
790-7035-12	3	Red	Steel	Screw	5	-
790-7036-10	3	Black	Copper	Screw	10	-
790-7036-12	3	Red	Copper	Screw	10	-
790-7005	2	Uninsul	Steel	Screw	5	790-7025-XX*
790-7007	2	Uninsul	Copper	Screw	10	790-7025-XX*
790-7030-10	4	Black	Steel	Solder	5	-
790-7030-12	4	Red	Steel	Solder	5	-

MINIATURE ALLIGATOR CLIPS


PART NO.	FIG.	INSUL COLOR	CLIP MATERIAL	WIRE CONNECT	RATED Amps	INSULATORS SOLD SEPARATELY
790-7020	5	Uninsul	Steel	Solder	1	790-7027-XX*
790-7021	5	Uninsul	Copper	Solder	1	790-7027-XX*

STANDARD ADAPTER

PART NO.	FIG.	INSUL COLOR	CLIP MATERIAL	WIRE CONNECT	RATED Amps	INSULATORS SOLD SEPARATELY
790-7066	6	Uninsul	Steel	.080 Tip	5	790-7025-XX*

*SEE INDIVIDUAL INSULATOR P/N FOR STANDARD COLOR DESIGNATIONS.

BATTERY CLIP



STEEL, ELECTROPLATED

PART NO.	FIG.	CURRENT CAPACITY	SPREAD JAWS	LENGTH	SPRING	INSULATORS SOLD SEPARATELY
790-7101	2	5 Amp	3/8	1-5/8	7 lbs	790-7130-XX*
790-7102	4	10 Amp	9/16	2	10 lbs	790-7111-XX*
790-7103†	1	25 Amp	1	2-1/2	17 lbs	790-7109-XX*
790-7104†	1	50 Amp	1-1/2	3-7/8	33 lbs	790-7110-XX*
790-7105†	3	100 Amp	1-3/8	6	40 lbs	790-7112-XX*

SOLID COPPER


PART NO.	FIG.	CURRENT CAPACITY	SPREAD JAWS	LENGTH	SPRING	INSULATORS SOLD SEPARATELY
790-7106	4	40 Amp	5/8	2-1/2	17 lbs	790-7113-XX*
790-7107†	1	100 Amp	1-1/4	4-3/4	33 lbs	790-7110-XX*
790-7108†	3	200 Amp	1-3/8	5-3/4	40 lbs	790-7112-XX*

*SEE INDIVIDUAL INSULATOR P/N FOR STANDARD COLOR DESIGNATIONS.
† SOLD IN PAIRS, ONE POSITIVE AND ONE NEGATIVE, TO PURCHASE SEPARATELY, ADD "P" SUFFIX FOR POSITIVE OR "N" SUFFIX FOR NEGATIVE TO PART NUMBER.

PLIER TYPE BATTERY CLIPS

INSULATED VINYLITE HANDLES, RED OR BLACK- SPECIFY COLOR

PART NO.	Amps	MATERIAL	SIZE	COLOR
790-7120-10	35	Steel, Cop. Pl.	3-1/4	BLACK
790-7120-12	35	Steel, Cop. Pl.	3-1/4	RED
790-7121-10	50	Steel, Cop. Pl.	2-13/16	BLACK
790-7121-12	50	Steel, Cop. Pl.	2-13/16	RED
790-7122-10	100	Steel, Cop. Pl.	7-1/2	BLACK
790-7122-12	100	Steel, Cop. Pl.	7-1/2	RED
790-7123-10	300	Solid, Copper	7-1/2	BLACK
790-7123-12	300	Solid, Copper	7-1/2	RED



790-70XX-XX

790-71XX-XX

BASIC PART NO COLOR





FIG. #3

FIG. #2

INSULATOR BOOTS

STANDARD COLOR RED AND BLACK OTHER COLORS AVAILABLE ON SPECIAL ORDER

	12	10	14	15	16	19
	RED	BLACK	YELLOW	GREEN	BLUE	WHITE
PART NO.	FIG.	COLOR	MATERIAL	A	B I.D.	C I.D.
790-7025-10	1	BLACK	VINYL	2-1/32	13/32	7/32
790-7025-12	1	RED	VINYL	2-1/32	13/32	7/32
790-7026-10	1	BLACK	VINYL	1-5/8	1/4	.22
790-7026-12	1	RED	VINYL	1-5/8	1/4	.22
790-7113-10	2	BLACK	VINYL	3-1/2	19/32	15/64
790-7113-12	2	RED	VINYL	3-1/2	19/32	15/64
790-7027-10	3	BLACK	VINYL	1-7/32	1/8	19/64
790-7027-12	3	RED	VINYL	1-7/32	1/8	19/64
790-7111-10	2	BLACK	VINYL	2-9/16	1/2	13/64
790-7111-12	2	RED	VINYL	2-9/16	1/2	13/64
790-7110-10	2	BLACK	VINYL	5	1-13/32	33/64
790-7110-12	2	RED	VINYL	5	1-13/32	33/64
790-7112-10	2	BLACK	VINYL	6-13/16	1-3/4	41/64
790-7112-12	2	RED	VINYL	6-13/16	1-3/4	41/64
790-7130-10	2	BLACK	VINYL	2-1/64	27/64	5/32
790-7130-12	2	RED	VINYL	2-1/64	27/64	5/32
790-7109-10	2	BLACK	VINYL	3-7/8	1-1/64	19/64
790-7109-12	2	RED	VINYL	3-7/8	1-1/64	19/64

CONCORD