



Specifications
 Current Rating: 3Amp
 Insulation Resistance: 1000MΩ Min.
 Dielectric Withstanding: 600V AC/DC
 Contact Resistance: 20mΩ Max.
 Operating Temperature: -40°C to +105°C

Materials

Contact Material: Copper Alloy
 Insulation Material: Polyester, UL 94V-0
 P.B.T
 Contact plating: Gold Flash

All materials must be GP materials



NUMBER OF POSITIONS	Dimensions		
	A	B	C
10	32.00	21.84	10.16
14	37.08	26.92	15.24
16	39.62	29.46	17.78
20	44.70	34.54	22.86
26	52.32	42.16	30.48
30	57.40	47.24	35.56
34	62.48	52.32	40.64
40	70.10	59.94	48.26
50	82.80	72.64	60.96
60	95.50	85.34	73.66
64	100.58	90.42	78.74

CnC Tech, LLC

Industrial Cable and Connector Technology

DESIGN	<i>lumayc</i>	PART NO.	3010-XX-001-12-00		
DATE	2011.12.05	REV	A	SIZE	A4
CHECKED		UNIT	mm		UNLESS OTHERWISE SPECIFIED TOLERANCES ANG 0 .0 .00 ±.5° ±0.3 ±0.15 ±0.10