

[Home](#) > [Search Engine](#) > Catalog: TZB4R500AB10B00

Capacitors > Ceramic Trimmer Capacitors

 How to check EU RoHS Compliance of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specification

Global Part Number	TZB4R500AB10B00
Previous Part Number	TZBX4R500BA110
Cmin. (max.)	7.0pF
Cmax.	50.0pF +100/-0%
TC	N750±300ppm/°C
Q	300min. at 1MHz, Cmax
Rated Voltage	50Vdc
Withstanding Voltage	110Vdc
Insulation Resistance (min.)	10000M ohm
Torque	1.5 to 9.8mNm
Operating Temperature Range	-25 to +85°C
Stator/Case Color	Black+Marking
Adjustment Direction	Top
Soldering Method	Flow/Reflow
Height	3mm ±0.2
Weight	0.15g

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	500
Ammo Pack	
320Reel	
Magazine	

Details

-  [Part Numbering](#)
-  [Appearance](#)
-  [Dimensions](#)
-  [Features and Applications](#)
-  [Temp. Coeff. Characteristics](#)
-  [Frequency Characteristics](#)
-  [Construction](#)
-  [Land Pattern](#)
-  [Notice \(Storage and operating condition\)](#)
-  [Notice \(Soldering and mounting\)](#)
-  [Notice \(Handling\)](#)
-  [Notice \(Other\)](#)
-  [Soldering Profile](#)

Box	
-----	--

Please approve our product specifications or to transact the approval sheet for product specifications before ordering. Please read rating and !Cautions first.

Product specifications in this catalog are as of November 2008.

Please make sure to read the Murata's [Product Policy](#) ,too.

All products and company names herein are trademarks or registered trademarks of their respective owners.

UP 

| [Site Map](#) | [History](#) | [Terms of use](#) | [Privacy Policy](#) |

All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd. 2008