






MATE 0.64SQ. POST
0.64角 ポストと嵌合



SECT. A-A



SECT. B-B



- 注 記:
1. 使用ハウジング型番: 917686/917697
 2. 製品規格: 108-5459
 3. 取付適用規格: 114-5203

- NOTES:
1. USE HOUSING P/N 917686/917697
 2. PRODUCT SPEC. ; 108-5459
 3. APPLICATION SPEC. ; 114-5203

PRE TINNED PHOSPHOR BRONZE (0.2t) 鍍めつき黄銅青銅 (板厚0.2)				C-917684-1			
MATERIAL & FINISH 材質及び仕上げ				PART NO. 型番			
適合電線断面 (WIRE RANGE) 0.12 - 0.35mm ² (AWG#28-#22)				絶縁外径 (INSULATION DIA.) 0.93 - 1.5 mmφ			
材質 (MATERIAL) 表参照				仕上 (FINISH) 表参照			
DR. 20 MAY. '95 Y. NOGUCHI				DE. 20 MAY. '95 Y. NOGUCHI			
CHK. 20 MAY. '95 Y. KASHIWA				APP. 20 MAY. '95 Y. KASHIWA			
A1 REVISED PER ECO-11-005140				RK HMR 01APR 11			
LTR 変更 (REVISION RECORD)				DR CHK DATE			
名 (NAME) 2.5mm シグナルダブルロック リセブタクル コンタクト (M) 2.5mm SIGNAL DBL-LOCK REC. CONT.				公差 (TOLERANCE) 10 MY ± 0.2 10 MM 30 MY ± 0.25 30 MM 100 MY ± 0.3 角度 ± 3°			
B J				LOC 番 (No.) C-917684			
R (SCALE) 10-1				REV. A1 SHEET 1 OF 1			