



Part Number	Pieces Per Package	Material	Color	Labels Per Row	Label Width Inch (mm) A	Label Height Inch (mm) B	Horizontal Repeat Inch (mm) C	Vertical Repeat Inch (mm) D	Web Width Inch (mm) E	Recommended Ribbon
0.500" Label Width										
THT-144-499-3●	3,000	Nylon Cloth	White	3	0.500 (12.70)	dia.	0.600 (15.24)	0.625 (15.88)	1.900 (48.26)	R4302
THT-36-422-10	10,000	Polyester	White	5	0.500 (12.70)	0.200 (5.08)	0.625 (15.88)	0.300 (7.62)	3.200 (81.28)	R6002
THT-36-423-10	10,000	Polyester	White	5	0.500 (12.70)	0.200 (5.08)	0.625 (15.88)	0.300 (7.62)	3.200 (81.28)	R6002
THT-36-473-10	10,000	Polyester	White	5	0.500 (12.70)	0.200 (5.08)	0.625 (15.88)	0.300 (7.62)	3.200 (81.28)	R6002
THT-97-423-10	10,000	Polyester	White	1	0.500 (12.70)	0.200 (5.08)	—	0.300 (7.62)	0.700 (17.78)	R6011
THT-97-457-10	10,000	Polyimide	White	1	0.500 (12.70)	0.200 (5.08)	—	0.300 (7.62)	0.700 (17.78)	R6011
THT-97-473-10	10,000	Polyester	White	1	0.500 (12.70)	0.200 (5.08)	—	0.300 (7.62)	0.700 (17.78)	R6011
THT-97-477-10	10,000	Polyimide	White	1	0.500 (12.70)	0.200 (5.08)	—	0.300 (7.62)	0.700 (17.78)	R6011
THT-97-478-10	10,000	Polyimide	White	1	0.500 (12.70)	0.200 (5.08)	—	0.300 (7.62)	0.700 (17.78)	R6011
THT-97-479-10	10,000	Polyimide	White	1	0.500 (12.70)	0.200 (5.08)	—	0.300 (7.62)	0.700 (17.78)	R6011
THT-97-487-10	10,000	Polyimide	White	1	0.500 (12.70)	0.200 (5.08)	—	0.300 (7.62)	0.700 (17.78)	R6011
THT-97-495-10	10,000	PEN	White	1	0.500 (12.70)	0.200 (5.08)	—	0.300 (7.62)	0.700 (17.78)	R6011
THT-97-497-10	10,000	Polyimide	White	1	0.500 (12.70)	0.200 (5.08)	—	0.300 (7.62)	0.700 (17.78)	R6011
THT-96-354-10	10,000	Polyester/Paper	White	4	0.500 (12.70)	0.275 (6.99)	0.600 (15.24)	0.375 (9.53)	2.500 (63.50)	R6200
THT-96-473-10	10,000	Polyester	White	4	0.500 (12.70)	0.275 (6.99)	0.600 (15.24)	0.375 (9.53)	2.500 (63.50)	R6000
THT-96-477-10	10,000	Polyimide	White	4	0.500 (12.70)	0.275 (6.99)	0.600 (15.24)	0.375 (9.53)	2.500 (63.50)	R6000
THT-96-487-10	10,000	Polyimide	White	4	0.500 (12.70)	0.275 (6.99)	0.600 (15.24)	0.375 (9.53)	2.500 (63.50)	R6000
THT-96-497-10	10,000	Polyimide	White	4	0.500 (12.70)	0.275 (6.99)	0.600 (15.24)	0.375 (9.53)	2.500 (63.50)	R6000
THT-148-422-10	10,000	Polyester	White	4	0.500 (12.70)	0.375 (9.50)	0.600 (15.24)	0.475 (12.07)	2.500 (63.50)	R6002
THT-148-430-10	10,000	Polyester	Clear	4	0.500 (12.70)	0.375 (9.50)	0.600 (15.24)	0.500 (12.70)	2.500 (63.50)	R6002
THT-12-351-10	10,000	Tamper-Resistant Vinyl	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6202
THT-12-423-10	10,000	Polyester	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-426-10	10,000	Polyimide	Amber	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R4300
THT-12-428-10	10,000	Metallized Polyester	Silver	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R4300
THT-12-433-10	10,000	Removable Polyester	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-435-10	10,000	Glossy Metallized Polyester	Silver	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-438-10	10,000	Tamper-Evident Polyester	Silver	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R4300
THT-12-457-10	10,000	Polyimide	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-473-10	10,000	Polyester	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-477-10	10,000	Polyimide	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-478-10	10,000	Polyimide	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-479-10	10,000	Polyimide	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-487-10	10,000	Polyimide	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-495-10	10,000	PEN	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-12-497-10	10,000	Polyimide	White	5	0.500 (12.70)	0.437 (11.10)	0.662 (16.81)	0.537 (13.64)	3.350 (85.09)	R6002
THT-149-358-10	10,000	Tamper-Resistant Acetate	Clear	4	0.500 (12.70)	0.500 (12.70)	0.600 (15.24)	0.600 (15.24)	2.500 (63.50)	R6202
THT-99-359-10	10,000	Tamper-Resistant Acetate	White	4	0.500 (12.70)	0.500 (12.70)	—	0.600 (15.24)	0.700 (17.78)	R6211
THT-149-422-10	10,000	Polyester	White	4	0.500 (12.70)	0.500 (12.70)	0.600 (15.24)	0.600 (15.24)	2.500 (63.50)	R6002
THT-149-430-10	10,000	Polyester	Clear	4	0.500 (12.70)	0.500 (12.70)	0.600 (15.24)	0.605 (15.38)	2.500 (63.50)	R6002
THT-99-473-10	10,000	Polyimide	White	1	0.500 (12.70)	0.500 (12.70)	—	0.600 (15.24)	0.700 (17.78)	R6011
THT-99-477-10	10,000	Polyimide	White	1	0.500 (12.70)	0.500 (12.70)	—	0.600 (15.24)	0.700 (17.78)	R6011
THT-99-478-10	10,000	Polyimide	White	1	0.500 (12.70)	0.500 (12.70)	—	0.600 (15.24)	0.700 (17.78)	R6011
THT-99-479-10	10,000	Polyimide	White	1	0.500 (12.70)	0.500 (12.70)	—	0.600 (15.24)	0.700 (17.78)	R6011
THT-99-487-10	10,000	Polyimide	White	1	0.500 (12.70)	0.500 (12.70)	—	0.600 (15.24)	0.700 (17.78)	R6011
THT-99-495-10	10,000	PEN	White	1	0.500 (12.70)	0.500 (12.70)	—	0.600 (15.24)	0.700 (17.78)	R6011
THT-99-497-10	10,000	Polyimide	White	1	0.500 (12.70)	0.500 (12.70)	—	0.600 (15.24)	0.700 (17.78)	R6011
THT-149-7566-10	10,000	Tamper-Evident Polyester	Clear	4	0.500 (12.70)	0.500 (12.70)	0.600 (15.24)	0.600 (15.24)	2.500 (63.50)	R6002
THT-68-498-10	10,000	Vinyl Cloth	White	4	0.500 (12.70)	0.750 (19.05)	0.600 (15.24)	0.850 (21.59)	2.500 (63.50)	R4300
THT-68-499-10	10,000	Nylon Cloth	White	4	0.500 (12.70)	0.750 (19.05)	0.600 (15.24)	0.850 (21.59)	2.500 (63.50)	R4902
THT-87-498-10	10,000	Vinyl Cloth	White	6	0.500 (12.70)	1.440 (36.50)	0.600 (15.24)	1.562 (39.68)	3.700 (93.98)	R4300
0.590" Label Width										
DSTHT-15-390-1	1,000	Polypropylene	White	1	0.590 (15.00)	0.163 (4.14)	—	0.402 (10.21)	—	R6200
DSTHT-15-390-2.5	2,500	Polypropylene	White	1	0.590 (15.00)	0.163 (4.14)	—	0.402 (10.21)	—	R6200

Note: Labels in chart are sorted in order by width, height, 3 or 4 digit material number (within part number), then die number (within part number).