

TouchBoard

G80-11900



Facts & Features

- Single keys with Gold Crosspoint contacts (Cherry MX Modules)
- Designed for continuous use - > 50 Mio key presses
- Robust and reliable
- Space-saving and ergonomic
- Integrated Touchpad plus 2 mouse buttons
- Usable with standard drivers of the operating system
- Ideal for industrial usage and for 19" applications
- Programmable keys (USB version)

Agency Approvals

- CE, VDE, cURus, FCC, VCCI, BSMI (PS/2 version), WHQL
- Designed for Windows™ 2000 and XP
- MS Windows™ Vista, Linux compliant

System Requirements

- PS/2: IBM- or compliant system
PS/2 plugs for keyboard and mouse
- USB: USB plug & supporting operating system
For KeyM@n software:
MS Windows™ 2000, XP or Vista

Delivery Volume

- Keyboard, printed manual
- Adaptor PS/2 → DIN(AT) (Combo version)
- Adaptor PS/2 → RS232 (Combo version)

Technical Data

- Number of Keys
104 = international layout
105 = european layout
- Cable Length
approx. 1.75 m
- Weight
approx. 1000 g (keyboard)
approx. 1200 g (with packaging)
- Dimensions
approx. 415 x 193 x 37 mm (keyboard)
approx. 450 x 245 x 45 mm (packaging)
- Interface
USB 2.0 (1.1 compatible) or PS/2
- Current Input
PS/2: approx. 35 mA (keyboard)
approx. 3 mA (Touchpad)
USB: max. 100mA
- Touchpad
Resolution: 1000 dpi
Lifetime (Overlay): > 10 Mio. strokes
- Reliability
MCBF > 10⁹ operations
MTBF > 100.000 hours
- Operating life time of individual keys
> 50 Mio operations
- Storage Temperature
-20 °C to +60 °C
- Operating Temperature
0 °C to +50 °C
- Packaging Unit
66 keyboards per master carton
2 master cartons per pallet (132 pcs.)
- Warranty
2 years

TouchBoard USB Version:

Keys listed below can be programmed via Cherry KeyM@n software (SW macros; max. 3 layers):

Function keys F1 – F12; Insert; Delete; Home; End; Page Up; Page Down;
PrtScr; Break; Numpad Comma; Numpad 0

No support of extended configuration for the touchpad (via software).

Order Description

Order Number	Interface Keyboard	Interface Touchpad	Colour
G80-11900LUMxx-0	USB		light grey
G80-11900LUMxx-2	USB		black
G80-11900LPMxx-0	PS/2	PS/2	light grey
G80-11900LPMxx-2	PS/2	PS/2	black
G80-11900LTMxx-0	PS/2 (DIN(AT) via Adaptor)	PS/2 (RS 232 via Adaptor)	light grey
G80-11900LTMxx-2	PS/2 (DIN(AT) via Adaptor)	PS/2 (RS 232 via Adaptor)	black

The xx in the order number defines the country version:

Possible european layouts (105 keys):

BE Belgium
CH Switzerland
DE Germany
DK Denmark
ES Spain
FR France
GB UK-English
GR Greek
IT Italy
NO Norway
PO Portugal
SF Sweden / Finland
TS Czech Republic

Possible international layouts (104 keys):

EU US English with €
RB US-English / Cyrillic

Other country versions upon request.

Cherry GmbH
Cherrystraße
91275 Auerbach/Opf.
Germany

Phone: +49 9643 18 0
Internet: www.cherry.de

Sales: +49 1805 243779 (+49 1805 CHERRY)
E-Mail: sales@cherry.de
Fax: +49 9643 18 1545

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice.

Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2008 Cherry GmbH, Last update: 17. Jul 2008_V12

