





Miscellaneous Terminals

Button Contacts






Type	Wire Range		Insul. Dia.	Stock Thickness	Dimensions			Material	Part Number
	AWG	mm ²			W	L	E		
A	20-16	0.5-1.4	.090-.120 2.29-3.05	.016 0.41	.195 4.95	.240 6.10	—	Brass	42218-3 ¹
					.195 4.95	.310 7.87	—	Brass	61165-1 ²
					.240 6.10	.310 7.87	—	Tin Plated Brass	61165-2 ²
B	20-16	0.5-1.4	.090-.125 2.29-3.18	.016 0.41	.195 4.95	.235 5.97	—	Brass	61039-1
					.230 5.84	.175 4.45	.060 ³ 1.52	Tin Plated Brass	505034-1
					.230 5.84	.175 4.45	.060 ³ 1.52	Tin Plated Brass	505034-2 ²
C	20-16	0.5-1.4	—	.016 0.41	.195 4.95	.235 5.97	—	Brass	505034-3 ²
					.195 4.95	.235 5.97	—	Brass	61280-1
D	20-16	0.5-1.4	—	.020 0.51	.230 5.84	.175 4.45	.060 ³ 1.52	Brass	61280-2 ²
					.230 5.84	.175 4.45	.060 ³ 1.52	Brass	40662 ³

¹ fits .150 [3.81] dia hole

² alternate reeling direction for mini applicator compatibility

³ tab bent down in applicator

Grounding Clips



Type	Wire Range		Insul. Dia. Range	Application Panel Thk.	Stock Thk.	Dimensions			Material	Part Number
	AWG	mm ²				W	L	E		
A	18-14	0.8-2.0	.090-.125 2.29-3.18	.020-.030 0.51-0.76	.020 0.51	.140 3.56	.730 18.54	.382 9.70	Stainless Steel	63895-1
				.047-.057 1.19-1.45	.020 0.51	.190 4.83	.730 18.54	.382 9.70	Stainless Steel	1217012-1
				.020-.040 0.51-1.02	.020 0.51	.140 3.56	.620 15.75	.440 11.18	Tin Plated Steel	63733-1
B	22-18	0.3-0.8	—	.020-.040 0.51-1.02	.020 0.51	.140 3.56	.620 15.75	.440 11.18	Tin Plated Steel	63733-1
				.020-.040 0.51-1.02	.020 0.51	.140 3.56	.620 15.75	.440 11.18	Tin Plated Phos. Bronze	63733-2
C	18-14	0.8-2.0	.100-.140 2.54-3.56	.019-.071 0.48-1.80	.020 0.51	.615 15.62	.675 17.10	.440 11.18	Stainless Steel	63575-1