

System Overview

Vinyl Letters and Numbers



Material Chart

Material	Print Method	Temperature Range	Features
Vinyl (PVL) •	Pre-Printed	-50°F to 225°F (-46°C to 107°)	Indoor/outdoor rated; heavy duty material for flat applications and safety and facility identification; resistant to UV light, chemical atmosphere and abrasion

Labeling Solutions by Application

Labels by Print Method

Part Number	Legend	Legend Height		Height		Width		Color (Legend/Background)	Markers Per Card	Std. Pkg. Qty. Card(s)
		In.	mm	In.	mm	In.	mm			
PVL100BY-0	0	1.00	25.40	.88	22.35	1.50	38.10	Black/Yellow	10	25
PVL100BY-1 thru PVL100BY-9	1 thru 9									25
PVL100BY-A thru PVL100BY-Z	A thru Z									25
PVL100BY-DSH	—									25
PVL200BY-0	0	2.00	50.80	.88	22.35	2.25	57.15	Black/Yellow	10	25
PVL200BY-1 thru PVL200BY-9	1 thru 9									25
PVL200BY-A thru PVL200BY-Z	A thru Z									25
PVL200BY-DSH	—									25

Labeling Software

Printers

Pre-Printed and Write-On Markers

Vinyl Cloth Letters and Numbers



Material Chart

Material	Print Method	Temperature Range	Features
Vinyl Cloth, (PCL,PCLCP) •	Pre-Printed	-50°F to 170°F (-46°C to 77°C)	Indoor/outdoor rated; thin conformable material with repositionable adhesive allows label to be removed and reused or used in temporary applications; provides durability, high temperature resistance and dimensional stability for rough or textured surfaces

•UL Recognized. 

Lockout/Tagout

Safety and Facility ID

Generic Order Forms

Part Number	Legend	Legend Height		Width		Height		Color (Legend/Background)	Markers Per Card	Std. Pkg. Qty. Card(s)	Std. Ctn. Qty. Card(s)
		In.	mm	In.	mm	In.	mm				
PCL037-0	0	.38	9.65	.34	8.64	.75	19.05	Black/Yellow	78	25	100
PCL037-1 thru PCL037-9	1 thru 9									25	100
PCL037-0-9	0 thru 9									25	100
PCL037-A thru PCL037-Z	A thru Z									25	100
PCL037-A-Z	A thru Z	1	25.40	.34	8.64	.75	19.05	Black/Yellow	78	1	4
PCLCP037-A-Z	A thru Z									1	4
PCLCP037-0-9	0 thru 9									1	4

Standards

Technical Reference/ Index

Vinyl Cloth Letters and Numbers (continued)

Part Number	Legend	Legend Height		Width		Height		Color (Legend/Background)	Markers Per Card	Std. Pkg. Qty. Card(s)	Std. Ctn. Qty. Card(s)
		In.	mm	In.	mm	In.	mm				
PCL062-0	0	.63	16.00	.56	14.22	.75	19.05	Black/Yellow	32	25	100
PCL062-1 thru PCL062-9	1 thru 9									25	100
PCL062-A thru PCL062-Z	A thru Z									25	100
PCL062-A-Z	A thru Z									25	100
PCL062-DSH	—	1.00	25.40	.88	22.35	1.50	38.10	Black/Yellow	10	25	100
PCL100-0	0									25	100
PCL100-1 thru PCL100-9	1 thru 9									25	100
PCL100-0-9	0 thru 9									25	100
PCL100-A thru PCL100-Z	A thru Z									25	100
PCL100-A-J	A thru J									25	100
PCL100-K-T	K thru T									25	100
PCL100-U-Z	U thru Z									25	100
PCL100-DSH	—	2.00	50.80	.88	22.35	2.25	57.15	Black/Yellow	10	25	100
PCL200-0	0									25	100
PCL200-1 thru PCL200-9	1 thru 9									25	100
PCL200-0-9	0 thru 9									25	100
PCL200-A thru PCL200-Z	A thru Z									25	100
PCL200-A-J	A thru J									25	100
PCL200-K-T	K thru T									25	100
PCL200-U-Z	UK thru TZ									25	100
PCL200-DSH	—	3.00	76.20	1.50	38.10	3.50	88.90	Black/Yellow	6	25	100
PCL300-0	0									25	100
PCL300-1 thru PCL300-9	1 thru 9									25	100
PCL300-A thru PCL300-Z	A thru Z									25	100
PCL300-DSH	—									25	100

System
Overview

Labeling
Solutions
by
Application

Labels
by
Print
Method

Labeling
Software

Printers

Pre-Printed
and
Write-On
Markers

Lockout /
Tagout

Safety
and
Facility
ID

Generic
Order
Forms

Standards

Technical
Reference/
Index