

151-01105

High Torque Axial Mount, Bolt Hole Dia .327 in, PA66HIRHS, Black, 500/pkg

Article Number: 151-01105

Part Number: 151-01105

Type: SAM320B



[Find a Distributor](#)

[Order Samples](#)


[Get Technical Drawings](#)

| Share

Base Data

Part No.	151-01105
Type	SAM320B
Color	Black (BK)
Features	• Positions bundles off cross members and frame rails to prevent abrasion and chafing. • Metal insert bushing accommodates high torque installation. • Made with high impact, heat stabilized, and UV material ideal for trucking and heavy equipment environments.
Typical Application	High Torque Axial Mounts position bundles in the center of frame rails and cross members to prevent rubbing and chafing against hole edges. These mounts contain a metal bushing on the inside to accommodate high torque installation with high impact wrenches.

Product Dimensions



Length (L)	1.18" / 29.87mm
Width (W) (imperial)	0.96"
Width (W)	24.32mm
Height (H)	1.77" / 44.86mm
Max. Ø Bundle	2.0" / 50.8mm
Mounting Hole Ø	0.327" / 8.31mm

Material and Specifications

Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
Flammability	UL94 HB

Operating Temperature		-40 °F to +221 °F (-40 °C to +105 °C)
 Logistic and Packaging		
Packaging Type	bag	
Pkg. Qty.	500	
EAN code	4031026452173	
UPC	089306344032	

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)