


Rocker Switches and Power Slide Switches



CW's rocker and power slide switches utilize a unique patented sliding and rotating action that ensures contact cleanliness and extended life. The attractive style, quick-connect terminals and multiple agency listings make them the perfect choice

for your switch application. **Specifications.** **Housing Material:** Nylon (black). **Knob Material:** Nylon (black unless otherwise specified). **Terminals:** Copper. **Moving Contacts:** Copper. **Legend:** In white on rocker knob. UL, CSA and VDE.

| Stock No. | Mfr.'s Type     | Circuitry                 | Rating                         | EACH |       |       |         |
|-----------|-----------------|---------------------------|--------------------------------|------|-------|-------|---------|
|           |                 |                           |                                | 1-24 | 25-49 | 50-99 | 100-499 |
| 752-0015  | GRS-2011-2600   | SPST                      | 16 A @ 125 VAC; 12 A @ 250 VAC | .65  | .56   | .50   | .47     |
| 752-0049  | GRS-2011-2083   | SPST; (On/Off legend)     | 16 A @ 125 VAC; 12 A @ 250 VAC | .76  | .67   | .56   | .52     |
| 752-0050  | GRS-2011-2084   | SPST; (I/O legend)        | 16 A @ 125 VAC; 12 A @ 250 VAC | .76  | .67   | .56   | .52     |
| 752-0016  | GRS-2011B-2000* | SPST; Off/(Mom)On         | 13 A @ 125 VAC; 10 A @ 250 VAC | .82  | .71   | .59   | .55     |
| 752-0017  | GRS-2012-2600   | SPDT                      | 16 A @ 125 VAC; 12 A @ 250 VAC | 1.03 | .89   | .76   | .70     |
| 752-0018  | GRS-2013A-2600* | SPDT; On/Off/On           | 16 A @ 125 VAC; 12 A @ 250 VAC | 1.03 | .89   | .76   | .70     |
| 752-0019  | GRS-2013C-1300* | SPDT; (Mom)On/Off/(Mom)On | 13 A @ 125 VAC; 10 A @ 250 VAC | 1.07 | .93   | .78   | .72     |
| 752-0051  | GRL-2011-1600   | SPST; (Illuminated-Red)   | 16 A @ 125 VAC; 12 A @ 250 VAC | 1.62 | 1.40  | 1.18  | 1.09    |

|          |                 |                           |                                |      |      |      |      |
|----------|-----------------|---------------------------|--------------------------------|------|------|------|------|
| 752-0020 | GRS-4011-1600   | SPST                      | 16 A @ 125 VAC; 16 A @ 250 VAC | .76  | .66  | .61  | .56  |
| 752-0021 | GRS-4011-0040   | SPST; (Red knob)          | 16 A @ 125 VAC; 16 A @ 250 VAC | .76  | .66  | .61  | .56  |
| 752-0022 | GRS-4011-0076   | SPST; (I/O legend)        | 16 A @ 125 VAC; 16 A @ 250 VAC | .94  | .82  | .68  | .63  |
| 752-0023 | GRS-4011B-1300* | SPST; Off/(Mom)On         | 13 A @ 125 VAC; 10 A @ 250 VAC | .94  | .82  | .69  | .64  |
| 752-0024 | GRS-4012-1600   | SPDT                      | 16 A @ 125 VAC; 16 A @ 250 VAC | .88  | .76  | .64  | .59  |
| 752-0025 | GRS-4012-0026   | SPDT; (Red knob)          | 16 A @ 125 VAC; 16 A @ 250 VAC | .88  | .76  | .64  | .59  |
| 752-0026 | GRS-4013A-1300* | SPDT; On/Off/On           | 13 A @ 125 VAC; 10 A @ 250 VAC | 1.10 | .96  | .80  | .74  |
| 752-0027 | GRS-4013C-1300* | SPDT; (Mom)On/Off/(Mom)On | 13 A @ 125 VAC; 10 A @ 250 VAC | 1.10 | .96  | .80  | .74  |
| 752-0028 | GRS-4021B-0000* | DPST; Off/(Mom)On         | 13 A @ 125 VAC; 10 A @ 250 VAC | 1.31 | 1.14 | .96  | .89  |
| 752-0029 | GRS-4022-1600   | DPDT                      | 16 A @ 125 VAC; 16 A @ 250 VAC | 1.28 | 1.12 | .94  | .87  |
| 752-0030 | GRS-4022-0010   | DPDT; (Red knob)          | 16 A @ 125 VAC; 16 A @ 250 VAC | 1.28 | 1.12 | .94  | .87  |
| 752-0031 | GRS-4022-0013   | DPDT; (I/O legend)        | 16 A @ 125 VAC; 16 A @ 250 VAC | 1.38 | 1.19 | 1.00 | .93  |
| 752-0032 | GRS-4023A-1300* | DPDT; On/Off/On           | 13 A @ 125 VAC; 10 A @ 250 VAC | 1.47 | 1.28 | 1.07 | .99  |
| 752-0033 | GRS-4023C-1300* | DPDT; (Mom)On/Off/(Mom)On | 13 A @ 125 VAC; 10 A @ 250 VAC | 1.49 | 1.29 | 1.08 | 1.00 |
| 752-0052 | GRL-4011-1600   | SPST; (Illuminated-Red)   | 16 A @ 125 VAC; 16 A @ 250 VAC | 2.00 | 1.74 | 1.46 | 1.35 |

|          |              |                    |                                |      |      |      |      |
|----------|--------------|--------------------|--------------------------------|------|------|------|------|
| 752-0053 | GR-2022-1600 | DPDT               | 16 A @ 125 VAC; 12 A @ 250 VAC | 1.97 | 1.71 | 1.43 | 1.33 |
| 752-0054 | GR-2022-0007 | DPDT; (I/O legend) | 16 A @ 125 VAC; 12 A @ 250 VAC | 2.04 | 1.76 | 1.48 | 1.37 |

|          |              |      |                                |     |     |     |     |
|----------|--------------|------|--------------------------------|-----|-----|-----|-----|
| 752-0055 | G-2012-1315* | SPDT | 13 A @ 125 VAC; 10 A @ 125 VAC | .90 | .79 | .66 | .61 |
|----------|--------------|------|--------------------------------|-----|-----|-----|-----|

\*UL and CSA only.

Slide Switches

CW's miniature and standard-sized slide switches are adaptable to a host of applications..they are highly versatile, extremely reliable, and very economical. **Specifications.** **Housing Material:** Steel (nylon for G-107 and G-105). **Contacts:** Copper. **Button:** Nylon (black). UL and CSA except for Micro-Miniature slide switches (UL only).

| Stock No. | Mfr.'s Type   | Fig. | Circuitry | Terminal | Rating           | Dimensions — In. |       |       |       | EACH |       |       |         |
|-----------|---------------|------|-----------|----------|------------------|------------------|-------|-------|-------|------|-------|-------|---------|
|           |               |      |           |          |                  | A                | B     | C     | D     | 1-24 | 25-49 | 50-99 | 100-499 |
| 752-0034  | GF-1123-1110  | 1    | SPST      | PC       | 11.0 A @ 125 VAC | 1.360            | 0.550 | 1.125 | 0.344 | 1.01 | .88   | .74   | .67     |
| 752-0035  | GF-1126-1110  | 1    | DPDT      | PC       | 11.0 A @ 125 VAC | 1.360            | 0.550 | 1.125 | 0.344 | 1.14 | .99   | .83   | .77     |
| 752-0036  | GF-1128S-1110 | 1    | DP3POS    | PC       | 11.0 A @ 125 VAC | 1.656            | 0.550 | 1.406 | 0.344 | 1.30 | 1.12  | .94   | .87     |
| 752-0037  | GF-624-6014   | 1    | SPDT      | Solder   | 6.0 A @ 125 VAC  | 1.360            | 0.550 | 1.125 | 0.344 | .53  | .45   | .38   | .35     |
| 752-0056  | G-660S-6010   | 1    | 4P3POS    | PC       | 6.0 A @ 125 VAC  | 1.656            | 1.000 | 1.406 | 0.344 | 1.42 | 1.29  | 1.09  | 1.01    |
| 752-0038  | GF-642-6010   | 1    | 4PDT      | PC       | 6.0 A @ 125 VAC  | 1.360            | 1.000 | 1.125 | 0.344 | 1.08 | .94   | .79   | .73     |
| 752-0040  | GG-350-3010   | 2    | DPDT      | PC       | 3.0 A @ 125 VAC  | 1.360            | 0.550 | 1.125 | 0.515 | .60  | .53   | .44   | .40     |

|          |              |   |        |        |                 |       |       |       |       |      |      |     |     |
|----------|--------------|---|--------|--------|-----------------|-------|-------|-------|-------|------|------|-----|-----|
| 752-0041 | GF-123-3011  | 1 | SPST   | Solder | 3.0 A @ 125 VAC | 1.000 | 0.400 | 0.812 | 0.200 | .53  | .45  | .38 | .35 |
| 752-0042 | GF-126-3011  | 1 | DPDT   | Solder | 3.0 A @ 125 VAC | 1.000 | 0.400 | 0.812 | 0.200 | .78  | .69  | .57 | .53 |
| 752-0043 | G-128S-3011  | 1 | DP3POS | Solder | 3.0 A @ 125 VAC | 1.190 | 0.400 | 1.000 | 0.200 | .90  | .79  | .66 | .61 |
| 752-0057 | G-141S-3011  | 1 | DP4POS | Solder | 3.0 A @ 125 VAC | 1.377 | 0.400 | 1.187 | 0.200 | .98  | .89  | .76 | .70 |
| 752-0058 | GF-161-3011  | 1 | 3PDT   | Solder | 3.0 A @ 125 VAC | 1.000 | 0.567 | 0.812 | 0.200 | 1.02 | .93  | .79 | .73 |
| 752-0059 | G-168S-3011  | 1 | 3P3POS | Solder | 3.0 A @ 125 VAC | 1.190 | 0.567 | 1.000 | 0.200 | 1.13 | 1.03 | .87 | .81 |
| 752-0044 | GI-152-3010  | 2 | DPDT   | PC     | 3.0 A @ 125 VAC | 1.000 | 0.404 | 0.812 | 0.200 | 1.06 | .92  | .77 | .71 |
| 752-0060 | GPI-152-3013 | 3 | DPDT   | PC     | 3.0 A @ 125 VAC | 1.000 | 0.404 | 0.812 | 0.200 | .91  | .83  | .70 | .65 |
| 752-0061 | GPI-154-3013 | 3 | DP3POS | PC     | 3.0 A @ 125 VAC | 1.170 | 0.404 | 1.000 | 0.200 | 1.08 | .98  | .83 | .77 |

|          |             |   |      |           |                 |       |       |       |       |      |      |     |     |
|----------|-------------|---|------|-----------|-----------------|-------|-------|-------|-------|------|------|-----|-----|
| 752-0045 | GS-113-0512 | 1 | DPDT | Round Pin | 0.5 A @ 125 VAC | 0.762 | 0.312 | 0.562 | 0.187 | 1.18 | 1.02 | .85 | .79 |
| 752-0046 | GS-115-0511 | 1 | SPDT | Flat Pin  | 0.5 A @ 125 VAC | 0.750 | 0.220 | 0.593 | 0.125 | 1.00 | .86  | .72 | .67 |
| 752-0047 | G-105-0513  | 4 | SPST | PC        | 0.5 A @ 125 VAC | 0.500 | 0.330 | 0.250 | 0.110 | .81  | .70  | .59 | .54 |
| 752-0048 | G-107-0513  | 5 | SPDT | PC        | 0.5 A @ 125 VAC | 0.505 | 0.305 | 0.255 | 0.140 | 1.30 | 1.13 | .95 | .88 |

