

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [70107-0050](#)
Status: **Active**
Overview: [SL™ Modular Connectors](#)
Description: SL™ Wire-to-Wire Panel Mount Crimp Housing, Single Row, Version B, with Mounting Ears, 16 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)

[Product Specification PS-70400 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [70107](#)
Application Signal, Wire-to-Wire
Overview [SL™ Modular Connectors](#)
Product Name SL™
UPC 800755031188

Physical

Circuits (maximum) 16
Color - Resin Black
Flammability 94V-0
Gender Male
Glow-Wire Compliant No
Material - Resin Polyester
Net Weight 3.397/g
Number of Rows 1
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 2.54mm
Temperature Range - Operating -40°C to +120°C

Material Info

Reference - Drawing Numbers

Product Specification PS-70400
Sales Drawing SD-70107-0036-0059



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[70107Series](#)

Mates With
[70066](#) SL™ Crimp Housing A, G and D
(Notes: Version C and H will not mate
to the 70107 housing series), [70400](#)
SL™ Insulation Displacement Connector
Assembly, Version G Housing, [70430](#) SL™
Single Row Receptacle, Version G

Use With
[70021](#)