



818-341-3355 | info@nmbtc.com
Quality Is Our Primary Component

[PRODUCTS](#)
[INDUSTRIES](#)
[ENGINEERING](#)
[DISTRIBUTION](#)
[PRESS & ARTICLES](#)
[COMPANY](#)
[CONTACT](#)
[RSS Feed](#)

Fans and Blowers

[Fans & Blowers Search](#)
[Motorized Impellers](#)
[AC Weather Resistant](#)
[White Papers](#)
[Part Numbering](#)
[Engineering Info](#)
[Cross Reference](#)
[Find Inventory](#)
[Distributors](#)
[Fan Accessories](#)
[RoHS](#)
[FAQs](#)
[Contact](#)

AC Axial Fans Part Numbering System

AC Axial Fans Part Numbering System

To show details, place the mouse cursor on each item of the part number. Click "Display All" button to show all details.

47	15	M	S	-	12	T	-	B	2	0	-	A	00	Display All
(1)	(2)	(3)	(4)		(5)	(6)		(7)	(8)	(9)		(10)	(11)	
1. Size				2. Thickness				3. Series			4. Motor Type			
24			60mm								P series	S	Shaded Pole	
31			80mm			10			25mm					
36			92mm			12			30mm		M series	C	Capacitor	
47			119mm			15			38mm				Run	
59			150mm											
5. Input Voltage				6. Termination		7. Bearing		8. Speed						
100V class		200V class												
10	100V	20	200V		W	Lead Wires	B	Ball Bearing			1 < 2 < 3 < 4 < 5			
12	115V	22	220V		T	Terminal					low	high		
		23	230V											
		24	240V											
9. Protection				10. Product Number				11. Individual Specification						
0	Impedance Protected			A	Standard 115V, 230V & 240V				00	Standard				
A	Thermal Protected			B	Standard 100V, 200V & 220V				01-99	Custom				
	(including 5915PC B30 only)			D	Custom casing, 115V-230V									
				K	Frameless									