



LOC	DIST	REVISIONS				
HM	00	P	LTR	DESCRIPTION	DATE	APVD
			A	RELEASE PER NPR	27 JAN 06	CSV JD
			B	REV ECD-09-000951	15JAN09	LH JB

1. DIMENSIONS IN [] ARE IN INCHES.
2. 0.5 dB MAX INSERTION LOSS.
3. 55 dB MIN RETURN LOSS.
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



15±0.15	[591±6]	1-5492065-5
10±0.15	[394±6]	1-5492065-0
1.5±0.05	[59.1±2.0]	5492065-6
5±0.08	[197±3]	5492065-5
4±0.08	[157±3]	5492065-4
3±0.05	[118±2]	5492065-3
2±0.05	[79±2]	5492065-2
1±0.05	[39±2]	5492065-1
L		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.S. VASU 27 JAN 06		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608						
		CHK J.DUNCAN 27 JAN 06								
DIMENSIONS: METERS [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD J.DUNCAN 27 JAN 06		NAME PIGTAIL, FIBER OPTIC, SINGLEMODE BUFFERED FIBER, AMP SC (NG), OPTIMATE						
		PRODUCT SPEC —								
		APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
		WEIGHT —		A3	00779	C-5492065	—			
MATERIAL —		FINISH —		CUSTOMER DRAWING				SCALE 1:1	SHEET 1 OF 1	REV B