







TOLERANCES
UNLESS OTHERWISE SPECIFIED : ± 0.3



PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	GLASS FILLED THERMOPLASTIC RATED (UL94V-0)	1	COLOR: BRACK
2	CONTACT	PHOSPHOR BRONZE	n	PLATING: TIN ALLOY
3	MOUNTING PLATE	BRASS	2	PLATING: TIN ALLOY

RECOMMENDED PC BOARD LAYOUT
(COMPONENT SIDE)

n: NO. OF CONTACTS
(10 TO 30, ONLY EVEN POS.)



CONNECTOR OUTLINE


NOTE
FLATNESS FOR CONTACT TERMINAL
AND MOUNTING PLATE MUST BE WITHIN 0.1.

				尺度 SCALE	×	単位 DIM. IN	mm	品名 PRODUCT NAME	FLOATING BOARD TO BOARD RECEPTACLE CONNECTOR (SMT)	
				設計 DESIGN	m. koga Aug. 2, 2001			型番 CAT. NO.	BTFW__R-3RST	
				製図 DRAWN				図番 DWG. NO.	JSA 95588	REV. 0
				検図 CHKD				S. Nakajima 8/2/01		
REV.	日付 DATE	変更内容 DESCRIPTION	承認 APPD	承認 APPD	S. Nakajima			FCI		


DF-123
REV.B

THIS FIGURE SHOW THE CONNECTOR MATING BY MAKING CENTER AS CRITERIA.

FLOATING ALLOWANCE MATING DIRECTION : ± 0.5
 PITCH DIRECTION : ± 0.8
 Z DIRECTION : ± 0.5




PITCH DIRECTION : ± 0.8




4				SCALE	χ	UNIT	mm	PRODUCT NAME	CROSS SECTION OF MATED CONDITION	
3				DESIGNED	99-6-10			CAT. NO.	BTFW__P-3SST/ BTFW__R-3RST	
2				DRAWN	m.koga			DWG. NO.	JSA 94532	REV. 0
1				CHECKED	K. Suda			 FRAMATOME CONNECTORS FCI JAPAN LTD.		
REV.	DATE	REVISED DESCRIPTION	APPROVED	APPROVED						

THIS FIGURE SHOW THE CONNECTOR MATING BY MAKING CENTER AS CRITERIA.

FLOATING ALLOWANCE MATING DIRECTION : ± 0.5
 PITCH DIRECTION : ± 0.8
 Z DIRECTION : ± 0.5



PITCH DIRECTION : ± 0.8



4				SCALE	χ	UNIT	mm	PRODUCT NAME	CROSS SECTION OF MATED CONDITION	
3				DESIGNED	99-6-10			CAT. NO.	BTFW_P-3SST/ BTFW_R-3RD7	
2				DRAWN	m.koga			DWG. NO.	JSA 95032	REV.
1				CHECKED						0
REV.	DATE	REVISED DESCRIPTION	APPROVED	APPROVED				 FRAMATOME CONNECTORS FCI JAPAN LTD.		