


5100H1/5 Series Panel Mounted Bi-Color LED Indicator

DESCRIPTION AND FEATURES



Features

- Will light red or green by reversing polarity.

Mounting: Will snap-fit in Ø.249/.254 hole in panels
 .031/.062 thick

Wire Leads: No. 24 AWG, 6" insulated, bonded strands,
 stripped 1/2"

Anode(+): Yellow lead for red light-blue lead anode for
 green light

Housing: Black Nylon

ELECTRO-OPTICAL CHARACTERISTICS

Part Number	Color	Typ. Intensity (mcd)	Rated Current (mA)	Continuous Forward Current Max. (mA)	Forward Voltage Typ. (V)	Forward Voltage Max. (V)	Peak Forward Current @ 1ms-300pps (A)	Peak Wavelength (nm)
5100H1/5	Red/Green	6	20	10	2.2	2.8	.06	650 Red/565 Green