




NOTES:

1. INSULATOR MATERIAL:
GLASS FILLED POLYESTER (PCT),
RATED UL 94V-0, COLOR BLACK.
2. CONTACT MATERIAL:
OUTER SHELL: BRASS ALLOY 360, 1/2 HARD, PER ASTM B16.
INNER CONTACT: BERYLLIUM COPPER, ALLOY 172, PER ASTM B194.
3. CONTACT PLATING:
OUTER SHELL: 80-120u" TIN/LEAD PER SAE AMS-P-81728
OUTER SHELL: 80-120u" TIN for LF VERSION
OVER 100u" NICKEL PER QQ-N-290.
INNER CONTACT: #4(30), 200u" TIN/LEAD PER SAE-AMS-P-81728
INNER CONTACT: #4(30), 200u" TIN for LF VERSION
OVER 50u" NICKEL PER QQ-N-290.
4. NUMBER OF POSITIONS.

rev	ecn no	dr	date
H	LS07-0271	HLE	2007/10/29
J	LS07-0299	HLE	2007/11/20
K	LS08-0038	STG	2008/02/01
L	LS08-0051	HLE	2008/02/11
-	-	-	-
-	-	-	-
g	LS07-0141	HLE	2007/05/21

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	inch
		TOLERANCES UNLESS OTHERWISE SPECIFIED		size	Scale
Dr	D-WOLFORD	2000/02/14	0.X	±0.1	1:1
Eng	A-VASBINDER	2000/02/14	0.XX	±0.1	
Chr	A-VASBINDER	2000/02/14	0.XX ±2°	±0.1	
Appr	A-VASBINDER	2000/02/14	Product family		ECN
		SOCKET		Spec ref	RELEASED
FCI		PRESS FIT DIP SOCKET		dwg no	Rev.
DPF		SEE TABLE		58707	L
catalog no		CUSTOMER		sheet 1 of 2	

REV F - 2006-04-17

1

2

3

4

A

B

C

D




A

B


C

D

STYLE "B"



998ZLF CONTACT

THIS HOLE PATTERN APPLIES TO BOTH
STYLE A AND STYLE B CONTACTS.

NOTES:

1. INSULATOR MATERIAL:
GLASS FILLED POLYESTER (PCT),
RATED UL 94V-0, COLOR BLACK.
2. CONTACT MATERIAL:
OUTER SHELL: PHOSPHOR BRONZE.
INNER CONTACT: BERYLLIUM COPPER.
3. CONTACT PLATING:
OUTER SHELL: 200u" TIN/LEAD PER SAE AMS-P-81728
OUTER SHELL: 200u" TIN for LEAD FREE VERSION
OVER 100u" NICKEL PER QQ-N-290.
INNER CONTACT: #4(30), 200u" TIN/LEAD PER SAE-AMS-P-81728
INNER CONTACT: #4(30), 200u" TIN for LEADFREE VERSION
OVER 100u" NICKEL PER QQ-N-290.
4. COMPLIANT PRESS FIT IN $\phi .040 \pm .003$ PLATED
HOLE, RECOMMENDED DRILL SIZE 1.15 MM
FOR .090 TO .130 THICK BOARD.

NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in 65-22-008.
- Packaging spec: see 65-14-920

rev	ecn no	dr	date
H	LS07-0271	HLE	2007/10/29
J	LS07-0299	HLE	2007/11/20
K	LS08-0038	STG	2008/02/01
L	LS08-0051	HLE	2008/02/11
-	-	-	-
-	-	-	-
G	LS07-0141	HLE	2007/05/21

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	inch
		TOLERANCES UNLESS OTHERWISE SPECIFIED		size A3	Scale 1:1
Dr	D-WOLFORD	2000/02/14	ANGULAR	0.X	±0.1
Eng	A-VASBINDER	2000/02/14	LINEAR	0.XX	±0.1
Chr	A-VASBINDER	2000/02/14	0.XX ±2°	0.XXX	±0.1
Appr	A-VASBINDER	2000/02/14	Product family	SOCKET	Spec ref RELEASED
FCI		PRESS FIT DIP SOCKET		dwg no 58707	Rev. L
title DPF		SEE TABLE		CUSTOMER	sheet 2 of 2
catalog no					

REV F - 2006-04-17

1

2

3

4