


DESCRIPTION: 96 Pin Din Straight Male Connector



Materials:
Insulator: Glass-Filled PBT U.L. rated 94V-0 - 230°C Process Temp.
Contacts: Brass / Gold Plated mating area / Tin on Tails
RoHS Compliant

Electricals:
Current Rating: 2 Amps
Dielectric Withstanding Voltage: AC 500V for 1 minute
Insulator Resistance: 1000M Ohms min. at 500V DC
Contact Resistance: 30 m Ohms max. at 100mA DC
Operating Temperature: -55°C to + 105°C

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: WAYNE ROBBINS		DATE: 3-28-05	
		CHECKED:		DATE:	
		SCALE:	SHEET 1 OF 1		REV 1
		DWG NO. 689-XXX-110R001			