








PANDUIT P/N	WEIGHT	SPLIT SLEEVE TYPE
NKSCM**	.10 lbs/10 pcs [45.6 g/10 pcs]	PHOSPHOR BRONZE
NKSCMZ**	.10 lbs/10 pcs [45.6 g/10 pcs]	ZIRCONIA

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR OF MODULE BASE, AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. MATERIALS:
 - a. MODULE BASE: ABS
 - b. ADAPTER HOUSING: POLYCARBONATE
 - c. SPLIT SLEEVE: PHOSPHOR BRONZE/ZIRCONIA
 - d. INNER LATCH: POLYETHERIMIDE
 - e. DUST CAP: THERMOPLASTIC ELASTOMER
4. COMPLIANT WITH TIA/EIA-604-3 (FOCIS-3) AND TIA/EIA-568-B.3
5. DIMENSIONS IN BRACKETS ARE METRIC [mm]



ISOMETRIC VIEW
SHOWN W/O DUST CAPS

										NETKEY FIBER OPTIC SIMPLEX SC ADAPTER MODULE CUSTOMER DRAWING					
											 TM CORP. TINLEY PARK, ILL 60477				
											ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES				
										THIRD ANGLE PROJECTION	SCALE NONE				
										DRAWN BY MC	REVIEW DRAWING NUMBERS				
										DATE 09-20-04	SEE NOTES				
R	10-14-04	MC		RELEASED TO PRODUCTION		02066-05					PART NO. NKSCM**/NKSCMZ**				
											DRAWING NO. 02066-05		SIZE A		
REV	DATE	BY	CHK	DESCRIPTION		ECN	- R	CUST	SUP	OTH	CHK'D				

