

## Power Supplies



OMRON®

### S8E1 Series

— NEW —

Low cost single output switching power supply. **Input Voltage:** 85-132 VAC. Built-in overload protection. FCC Class A, convection cooled. LED operation indicator. UL recognized, CSA certified.

834-5506. S8E1-01012D. 10 W, 1.0 A, 12 V output.....	EACH	42.00
834-5507. S8E1-01024D. 10 W, 0.5 A, 24 V output.....	EACH	42.00
834-5508. S8E1-01512D. 15 W, 1.3 A, 12 V output.....	EACH	50.00
834-5509. S8E1-01524D. 15 W, 0.7 A, 24 V output.....	EACH	50.00
834-5510. S8E1-02512D. 25 W, 2.1 A, 12 V output.....	EACH	63.00
834-5511. S8E1-02524D. 25 W, 1.1 A, 24 V output.....	EACH	63.00
834-5512. S8E1-05012D. 50 W, 4.2 A, 12 V output.....	EACH	88.00
834-5513. S8E1-05024D. 50 W, 2.1 A, 24 V output.....	EACH	88.00



### S82D Series — High-Power, Enclosed Switching Power Supply

— NEW —


S82D ideal for high-power applications. **Input Voltage:** 85 to 132 VAC or 170 to 264 VAC (selectable). Built-in fan for cooling. Built-in overvoltage and overload protection. Built-in remote sensing function corrects voltage drop in load wiring. Remote control function allows ON-OFF control with external signal.

834-5514. S82D-3024. 300 W, 14 A, 24 V output.....	EACH	778.00
834-5515. S82D-6024. 600 W, 27 A, 24 V output.....	EACH	1200.00


### S82K Series

Type S82K compact, plastic enclosed, general purpose switching power supplies are DIN rail mountable. **Universal Input Voltage:** 3, 7.5, 15, 30, 50 W — 85-264 VAC, 47-450 Hz; 90, 100 W — 85-132 VAC or 170-264 VAC, 47-450 Hz. Output-ON indicator. New Undervoltage Alarm Indicator incorporated within the unit (90 and 100 W also available with SPST output). UL 508 listed, US and Canada Class 2 approved, CSA certified, VDE approved and CE compliant.

834-4162. S82K-00324. 3 W, 0.13 A, 24 V output.....	EACH	53.00
834-4163. S82K-00724. 7.5 W, 0.3 A, 24 V output.....	EACH	60.00
834-3022. S82K-01524. 15 W, 0.6 A, 24 V output.....	EACH	83.00
834-3050. S82K-03024. 30 W, 1.3 A, 24 V output.....	EACH	125.00
834-3051. S82K-05024. 50 W, 2.1 A, 24 V output.....	EACH	143.23
834-4164. S82K-09024. 90 W, 3.75 A, 24 V output.....	EACH	185.00
834-2013. S82K-10024. 100 W, 4.2 A, 24 V output.....	EACH	197.00
834-2014. S82K-24024. 240 W, 10 A, 24 V output.....	EACH	340.00
834-5500. S82K-00312. 3 W, 0.25 A, 12 V output.....	EACH	53.00
834-5503. S82K-00712. 7.5 W, 0.6 A, 12 V output.....	EACH	60.00
834-5504. S82K-01512. 15 W, 1.2 A, 12 V output.....	EACH	83.00
834-5505. S82K-03012. 30 W, 2.5 A, 12 V output.....	EACH	125.00



UL508 Approved




### S82J Series

12

#### Covered Frame

**Covered Frame**  
General purpose, switching power supply, 120 VAC or 240 VAC or universal input models available, 3 year warranty. CE, UL, CSA, VDE.

834-2015. S82J-5124. 10 W, 0.5 A, 24 V, 120 VAC.....	EACH	45.00
834-2016. S82J-6124. 10 W, 0.5 A, 24 V, 240 VAC.....	EACH	45.00
834-2017. S82J-5224. 25 W, 1.1 A, 24 V, 120 VAC.....	EACH	67.00
834-2018. S82J-6224. 25 W, 1.1 A, 24 V, 240 VAC.....	EACH	67.00
834-6612. S82J-05024D. 50 W, 2.1 A, 24 V, 100-240 VAC.....	EACH	87.00
834-6613. S82J-10024D. 100 W, 4.5 A, 24 V, 100-240 VAC.....	EACH	133.00



#### Enclosed Frame

**Enclosed Frame**  
General purpose, switching power supply, 120 or 240 VAC (selectable). 3 year warranty. CE, UL, CSA, VDE.

834-2023. S82J-30024. 300 W, 14 A, 24 V, 120 or 240 VAC selectable.....	EACH	399.00
834-2024. S82J-60024. 600 W, 27 A, 24 V, 120 or 240 VAC selectable.....	EACH	620.00

### S8PS Series

Compact, metal frame, DIN track mount, industrial, switching power supply, 100-240 VAC, 10 year service life. CE, UL, CSA, VDE.

834-2025. S8PS-05024CD. 50 W, 2.1 A, 24 V Output.....	EACH	132.00
834-2026. S8PS-10024CD. 100 W, 4.5 A, 24 V Output.....	EACH	197.00
834-2027. S8PS-15024CD. 150 W, 6.5 A, 24 V Output.....	EACH	230.00
834-2029. S8PS-30024CD. 300 W, 14 A, 24 V Output.....	EACH	450.00



For Fast, Dependable Service, Make Just One Call — 1-800-433-5700

ALLIED ► 705