



Hex 10mm Male-Female Standoff



<< B24



B26 >>

Lyn-Tron Part ID: **SS5179-25.0-01**

Qty in Stock: **105**

Alternative Part Possibilities

Lyn-Tron Part ID	Qty In Stock
SS5179-25.0-00	0

This color represents the identical unplated part.

Conformity

Conforming:	RoHS WEEE REACH DFARS
Non Conforming:	N/A
Download Conformity Stmt	

Other Available Options

View	Material Specs
View	Finish App Summary
View	General Notes
Download	CAD Drawing
View CAD files with: Autodesk Brava	

Code	Description
☐ AA	Aluminum (RoHS Compliant)
☐ AL	Aluminum
☐ BR	Brass (RoHS Compliant)
☒ SS	Stainless Steel (RoHS Compliant)
☐ ST	Steel (RoHS Compliant)

Basic Part Number	Thread Size	"X" Length	"Y" Min. Full Thd Depth	Min. Body Length
☐ 5178	M3.5 x 0.6	6.35	9.53	12.7
☒ 5179	M4.0 x 0.7	9.53	11.1	15.0
☐ 5180	M5.0 x 0.8	9.53	12.7	16.5

Code	Length Value
☐ 06.0	6
☐ 08.0	8
☐ 10.0	10
☐ 11.0	11
☐ 12.0	12
☐ 13.0	13
☐ 14.0	14
☐ 16.0	16

Code	Plate Description pertaining to material SS
☐ 00	Unplated
☐ 00D	Unplated - 202 Thread Lock Dri Loc IFI 125 / 525
☐ 00F	Nylon Strip (Fill)
☐ 00H	Heat Treat - Unplated
☐ 00P	Nylon Patch - Unplated
☐ 00Q	Nylon Pellet - Unplated
☐ 00S	Marking Stamp - Unplated
☒ 01	Passivate ASTM-A967-05
☐ 011	Passivate (Nitric) ASTM-A967-05
☐ 012	Passivate with 96 Hour Salt Spray ASTM-B-117 2 hour salt spray
☐ 01D	Passivate - #202 Thread Lock Dri Loc IFI 125 / 525
☐ 01E	Passivate with Electro Polish ASTM-A967-05
☐ 01H	Passivate + Heat Treat ASTM-A967-05