Search Results

Evaluate
- Brochures
  - PDF-High Speed D ..
- FAQ's

Design a Solution
- Catalog Cut Sheet
  - PDF-F1RBZN-9608- ..
- Part Drawings
  - PDF-QuickNet HDQ ..
- Specification Sheets
  - PDF-QuickNet Cas ..
  - PDF-QuickNet HDQ ..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ Text Search: 'F1ASZN-9612-10F'

Your search criteria matched only one product, shown below

F1ASZN-9612-10F

Quicknet™ HDQ Series High Density Fiber Optic Cassettes:
- Mounts to standard 19" rack rails
- Low insertion loss of 0.5dB max, per optimized cassette and 0.75dB max. per standard cassette; ensures system meets IEEE 802.3ae max. channel loss specification of ≤ 2.6dB
- Return loss: ≥ 26dB
- Adapter housing colors follow TIA/EIA - 568-C.3 suggested color identification scheme
- Connect together with high-density female MTP* cable assemblies as interconnection network
- Significantly reduce installation time and labor by eliminating field connector termination
- Factory terminated, assembled, and 100% tested
- Insertion loss data provided on every fiber cassette
- Lifetime traceability of test data to a Q.C. number
- 10Gig OM3 50/125um fiber cassettes are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters and up to 550 meters for OM4 at 850 nm; backward compatible with all 50/125um (OM2) MPO or MTP system requirements

Quicknet™ Cassette Rear Cable Manager:
- Mounts horizontally to standard 19" rack rails
- Fiber Management Slack Spools can be used to manage MTP Interconnect Cable

Part Number	F1ASZN-9612-10F
RoHS Compliancy Status	Compliant
Note	Intended for use in fixed installations which are outside the scope of RoHS
Part Description	QuickNet™ HDQ Series High Density Fiber Optic Cassette; 1RU-Angled 96-fiber S-type labeling; 10Gb OM4 12-fiber MTP to LC Pre-terminated – flipped polarity.
Pricing Description	12 Fiber High Density OM4 Fiber Optic Angled Cassette
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	☐

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2012, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy