



PRODUCT NO.

SEE TABLE




mat'l. code				surface ISO1302 ✓		tolerance ISO1101 ISO406		projection 		product family MOD JACK			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
AJ	ELX-N-15334	Henry	07/18/13	angles	linear	0.X±0.3		mm		8 POS VERTICAL PC.B. MOD JACK ASSY			
—	—	—	—	—	—	0.XX±0.15		—					
AD	N08-0239	MHT	11/10/08	0'±2'	linear	0.XXX±0.05		scale 2.0					
AE	N08-0092	SH	M01/13/10	dr	JANET	2/22/00				dwg no	sheet, 1 of 3	size	
AF	ELX-N-010673	SH	M00	3/14/12	engr	M.CHENG	12/19/00			69255	A		
AG	ELX-N-13788	Henry	01/02/13	chr	M.CHENG	12/19/00	type			Product	Customer	Drawing	
AH	ELX-N-14061	Henry	02/18/13	appd	M.CHENG	12/19/00							
sheet index	revision	AJ	AJ	AJ									
sheet	sheet	1	2	3									



PRODUCT NO. ④	DIM. A	DIM. B	DIM. C	STYLE	POSITIONS LOADED	CONTACT PLATING ①	NOTES
69255-X01YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X02YLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	5u" Au + high performance lubricant	-
-X03YLF	-	-	15.62/0.615	UNKEYED	2,3,4,5,6,7	5u" Au + high performance lubricant	-
-X04YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X05YLF	-	-	15.62/0.615	UNKEYED	ALL	1.27um /50u" GXT	-
-X06YLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	1.27um /50u" GXT	-
-X07YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 5
-X08YLF	-	-	15.62/0.615	UNKEYED	3,4,5,6	5u" Au + high performance lubricant	-
-X09YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6
-X10YLF	-	-	13.62/0.536	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6



KEYWAY OPTION ON
69255-002LF & -006LF ONLY.



SPECIAL BEND REQUIRED BY
CUSTOMER FOR P/N 69255-001BLF



NOTES :

① SPECIAL PACKAGING.

② SOLDER TAIL LENGTH :

X = 0 [3.18 ±0.51 /0 .125 ±0.020]

X = 1 [8.13 ±0.51 /0 .320 ±0.020]

X = 2 [5.30 ±0.51 /0 .208 ±0.020]

X = 3 [3.70 ±0.51 /0 .145 ±0.020]

X = 4 [4.50 ±0.51 /0 .177 ±0.020]

[FOR X = 1 TO 4 , IF WIRE TRUE POSITION IS NOT APPLICABLE.]

[PACKAGING SPEC. IS GS-14-428

③ COLOR OF HOUSING :

Y = NIL (BLACK HOUSING)

Y = W (WHITE, RAL1013 HOUSING)

Y = G (GRAY, HOUSING)

④ SPECIAL REQUIREMENT :

SEE DETAIL C FOR P/N 69255-001B

FOR FEATURE DETAILS.

⑤ NO PANEL STOPS ON -X09Y AND -X10Y.

⑥ THIS PIN NUMBERING OPPOSITE TO

FCC, PART 68, SUB-PART F REQUIREMENTS

⑦ PART NUMBERS WITH LF IN THE END ARE LEAD FREE.

8 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATION AS DESCRIBED IN GS-22-008.

9 THE HOUSING TEMPERATURE WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A
1.5 MM MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.

⑩ PLATING OPTION:

MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code				surface	tolerance	projection	product family				
				ISO1302	ISO1101 ISO406		MOD JACK				
ltr	ecn no	dr	date	tolerances unless otherwise specified			title				
AJ	ELX-N-15334	Henry	07/18/13	angles	linear	0.X±0.3		8 POS VERTICAL PC.B. MOD JACK ASSY			
-	-	-	0.XX±0.15								
AD	N08-0239	MHT	11/10/08			0°±2'					0.XXX±0.05
AE	N09-0092	SH MNO	01/13/10	dr	JANET	2/22/00		dwg no		sheet, 2 of 3	size
AF	ELX-N-010675	SH MNO	3/14/12	enfr	M.CHENG	12/19/00		69255		A4	
AG	ELX-N-13786	Henry	01/02/13	chr	M.CHENG	12/19/00		type Product Customer Drawing			
AH	ELX-N-14061	Henry	02/18/13	appd	M.CHENG	12/19/00					
sheet	revision										
index	sheet										

PRODUCT NO. ④	DIM. A	DIM. B	DIM. C	STYLE	POSITIONS LOADED	CONTACT PLATING ①	NOTES
69255-X01YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X02YHLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	5u" Au + high performance lubricant	-
-X03YHLF	-	-	15.62/0.615	UNKEYED	2,3,4,5,6,7	5u" Au + high performance lubricant	-
-X04YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X05YHLF	-	-	15.62/0.615	UNKEYED	ALL	1.27um /50u" GXT	-
-X06YHLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	1.27um /50u" GXT	-
-X07YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 1
-X08YHLF	-	-	15.62/0.615	UNKEYED	3,4,5,6	5u" Au + high performance lubricant	-
-X09YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6
-X10YHLF	-	-	13.62/0.536	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6

MEETS PIP PROCESS PRODUCT NO.

mat'l. code				surface ISO1302	tolerance ISO1101 ISO406	projection 	product family MOD JACK
litr	ecr no	dr	date	tolerances unless otherwise specified			title
AJ	ELX-N-15334	Henry	7/18/13	angles	0.X±0.3	mm	8 POS VERTICAL
-	-	-	-	0.XX±0.15	0.XXX±0.05	scale 2.0	PC.B. MOD JACK ASSY
AD	N08-0239	MHT	11/10/08	0'±2"	JANET	2/22/00	dwg no
AE	N09-0092	SH	01/13/10	dr	M.CHENG	12/19/00	sheet, 3 of 3
AF	ELX-N-010675	SH	3/14/12	enfr	M.CHENG	12/19/00	size
AG	ELX-N-13786	Henry	01/02/13	chr	M.CHENG	12/19/00	69255
AH	ELX-N-14061	Henry	02/18/13	appd	M.CHENG	12/19/00	A4
sheet	revision						type
index	sheet						Product Customer Drawing