

Product Description

Sealed foam swabs

Economical general purpose swabs. Best solvent retention.

The most cost-effective swabs for general purpose applications. 100 ppi reticulated medical grade foam provides excellent particle entrapment. The open cell structure gives the best solvent holding ability of any style of swab. These swabs are free of adhesives or binders that could contaminate your process. Fiberless construction does not generate particles.

Handle Material: polypropylene

Head material: polyurethane foam


Sale units: 1 bag of 125 swabs
1 box of 20 bags

IT41050 Small




Swab length:	2.8"	7.2 cm
Handle width:	0.10"	2.6 mm
Head length:	0.40"	10.2 mm
Head thickness:	0.13"	3.3 mm
Head width:	0.14"	3.5 mm

IT44070 Small pointed



Swab length:	3.2"	8.0 cm
Handle width:	0.10"	2.4 mm
Head length:	0.39"	9.9 mm
Head thickness:	0.11"	2.7 mm
Head width:	0.13"	3.3 mm

IT48040 Micro flexible



Swab length:	2.7"	6.8 cm
Handle width:	0.09"	2.2 mm
Head length:	0.41"	10.5 mm
Head thickness:	0.10"	2.5 mm
Head width:	0.12"	3.0 mm