

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

H

REV & REDRAW / 0720-0777-95

28SEP95

ME

NB

AMP
WIRE RANGE16-14 AWG
SOLID OR STRANDED

INSULATION

BODY

4.09 MAX
[.161]3.18
[.125].079 MIN
[.031]

SERRATIONS

20.07 MAX
[.790]


1.WIRE INSUL DIA, 2.92-4.32 [.115-.170]

---	-----	-----
---	-----	-----
100	LOOSE PIECE, BOX SPL	8-324225-5
100	LOOSE PIECE, BOX	8-324225-1
2500	ON TAPE, REEL	2-324225-1
1000	LOOSE PIECE	324225
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm [in]

TOLERANCES UNLESS
OTHERWISE SPECIFIED.0 PLC ±-
1 PLC ±-
2 PLC ±0.13[.005]
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL

BODY, SLV, COPPER PER ASTM B 152

INSUL, NYLON, COLOR, BLUE

FINISH

BODY & SLV, TIN PLATE

PER MIL-T-10727

DWN
M ELLIS

28SEP95

CHK
C PRESNELL

28SEP95

APVD
N BIRCH

28SEP95

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

TERMINAL, SHUR PLUG, PIDG™,
WIRE SIZE, 16-14 AWG

SIZE

CAGE CODE

DRAWING NO

A3

00779

C-324225

SCALE 4:1

SHEET

1 OF 1

REV

H

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

CIRCULAR MIL AREA:
1.04mm²-2.62mm² [2050-5180]

SOLID OR STRANDED