

AMPHENOL RF PART NUMBER

031-6118

BNC Straight Crimp Plug for RG-58, 50 Ohm



PRODUCT IMAGE
COMING SOON

PRODUCT OVERVIEW

RF Connector, BNC Straight Crimp Plug for RG-58, 50 Ohm

Product Type	Connectors
Product Series	BNC
Status	Active

PRODUCT SPECIFICATIONS

Gender	Plug
Orientation	Straight
Termination Style	Cable - Crimp
Impedence (Ohms)	50
Body Finish	Nickel
Body Material	Brass
Contact Finish	Gold
Contact Material	Brass
Contact Termination Style	Crimp
Insulator Material	PTFE
Cable Group	C
Cable Type	Belden 9907, Belden B7806A, LMR-195, RG-141, RG-303, RG-58, RG-58A, RG-58B, RG-58C
Crimp Tool	CTL-3
Coupling Mechanism	Bayonet
Max Frequency (GHz)	4
Polarity	Standard

Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500
Weight (Grams)	10.44
Package Type	BAG

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------