

Direct Links

Cross Reference

RoHS/LF P/N search

Document & Drawing search

Application tooling

Services

Contact us

Distributor list

Pricing request

Order samples

Literature

Brochures & catalogs

Product documentation

Technical library

Start > Search=yaes14k -53* > **YAES14K53**

YAES14K53

16-14 NUCL. INS. RING #8

ACTIVE

Customer Drawing

RoHS compatible

Electrical division

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Download document

Literature

- > Power solutions Product Focus
- > INSULUG Brochures
- > Renewable Energy Products Brochure
- > EC&M Catalog
- > Connector Theory and Application Brochure

Application Tooling

- > Electrical Tooling

Specifications

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Strip length (Wire)	7/32 in.		
Stud Hole (Size)	#8		
Tongue Angle	Straight		
Tongue Width (in)	0.31 in.		
Wire Shroud	No		
Insulation Diameter (Max)	0.153 in.		
Physical			
Conductor Size	14 AWG 16 AWG		
Conductor Type	Commercial/Military Stranded Coppe		
Insulation Type	Radiation Resistant Kynar		
Color Code	Blue		
Conductor Size (Range)	16 AWG to 14 AWG		
Approvals / Certifications			
Military Listed	MIL-T-7928		
UL Listed	No		
CSA Certified	No		
Other Features			
Tongue Type	Ring		
UPC	78181002698		
Keyword	smltermHC		