


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
BUD INDUSTRIES INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT
THE WRITTEN PERMISSION OF BUD INDUSTRIES INC. IS PROHIBITED.

DWG. NO. SNC-3753	
ISSUE	REVISIONS
(A)	REVISED DESIGN 6-30-08 DAB
(B)	PER ECN #10404 12-4-08 DAB
(C)	PER ECN #10446 1-13-09 BT

MATERIAL:
BODY, COVER MOUNTING BRACKETS, COVER - 16 GA. [1.5mm] C.R.S.
INTERNAL PANEL - 14 GA. [2.0mm] C.R.S.
WALL MOUNTING BRACKETS - 14 GA. [2.0mm] STAINLESS STEEL
HARDWARE - STAINLESS STEEL
GASKET - .25 [6.35] THICK NEOPRENE (BLACK) OR EQUIVALENT
SEALING WASHERS - BLACK NEOPRENE OR EQUIVALENT

FINISH:
BODY & COVER - LIGHT GRAY SMOOTH POWDER COAT
INTERNAL PANEL - ZINC CHROMATE
WALL MOUNTING BRACKETS - NATURAL



RETAINING CLIP (4x)

SEALING WASHER (4x)

M5x0.8 CAPTIVE SCREW (4x)


SEE DETAIL "B" (INSIDE VIEW)

WELD & GRIND SMOOTH ALL CORNERS

NO GAP BETWEEN GASKET JOINT. OPTIONALLY JOINT MAY BE SEALED WITH ADHESIVE.


.50 TYP. [12.70]

DETAIL B
SCALE 2 : 2.75



INTERNAL PANEL DETAIL

FRONT VIEW (LESS COVER)



DETAIL A
SCALE 2 : 2.75

PARTS LIST			
UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES (MILLIMETERS)		CAD GENERATED DRAWING. DO NOT MANUALLY UPDATE.	
TOLERANCES: DECIMALS .001 .002 .003 .005 .010 .015 .020 .030 .040 .050 .060 .070 .080 .090 .100 .125 .150 .175 .200 .250 .300 .375 .500 .625 .750 .875 1.000 1.250 1.500 1.750 2.000 2.500 3.000 3.500 4.000 5.000 6.000 7.000 8.000 10.000		APPROVALS DATE	
MATERIAL		DAB 5-5-08	
FINISH		AS NOTED	
QTY.		USED ON	
DO NOT SCALE DRAWING		SCALE [CAD FILE]	

BUD INDUSTRIES INC.	
NEMA SHEET METAL BOX w/LIFT-OFF SCREW COVER	
SIZE DWG. NO. SNC-3753	REV.
1	SHEET 1 OF 1