




AC Crossaxial Blower

OAB30 series

Impeller: Aluminum Alloy
Motor: AC Shaded pole
Insulation Class: E.B.F
Insulation Withstand: AC 1500V/1 minute
Insulation Resistance: >100M ohm DC500V
Operating Temp: 0C ~ +45C

Bearing: *
Indicate "B" for Ball bearing
or "S" for sleeve*



Motor type: AC Shaded type motor 1 ϕ 2p

Spec. Model	Size (mm)			Rated Voltage V	Rated Frequency Hz	Rated Current A	Input Power W	Speed r.p.m.	Max Pressure mmAq	Maximum Air Flow m ³ /min	CFM	Noise dBA	Safety Approval			Weight g
	A	B	C										UL	TUV	CE	
OAB30098-11-1	98	108	154	120	50/60	0.11/0.09	8/7	2500/2900	0.8/1.1	0.4/0.5	14/17	21/24				390
OAB30098-22-1				230	50/60	0.07/0.05	8/7	2500/2900	0.8/1.1	0.4/0.5	14/17	21/24				
OAB30160-11-1	160	170	222	120	50/60	0.14/0.12	9/8	2700/3100	0.9/1.2	0.7/0.8	24/28	27/30				520
OAB30160-22-1				230	50/60	0.09/0.07	10/9	2700/3100	0.9/1.2	0.7/0.8	24/28	27/30				
OAB30198-11-1	198	208	260	120	50/60	0.14/0.12	9/8	2700/3100	1.0/1.3	0.9/1.0	32/35	27/30				540
OAB30198-22-1				230	50/60	0.09/0.07	11/9	2700/3100	1.0/1.3	0.9/1.0	32/35	27/30				
OAB30300-11-1	300	310	366	120	50/60	0.20/0.17	15/13	2700/3100	1.4/1.7	1.5/1.7	53/60	32/34				670
OAB30300-22-1				230	50/60	0.09/0.07	12/11	2700/3100	1.4/1.7	1.5/1.7	53/60	32/34				

