

SEMELAB

SEMELAB LTD T-27-01

BI-POLAR TRANSISTORS (CECC AND HIGH REL) & HIGH ENERGY

Type Number	Rel Code	Pol	Package	V _{ceo}	I _c (cont)	H _{fe}	@ V _{ce} /I _c	f _T	P _d
BUL50A		NPN	SOT93	550	15	10min	4/5	20M	125
BUL50B		NPN	TO220	400	15	10min	4/5	20M	125
BUL51A		NPN	SOT93	300	30	30min	4/5		125
BUL51B		NPN	SOT93	250	40			20M	125
BUL52A		NPN	TO220	500	4				60
BUL52B		NPN	TO220	400	4	12min	4/1	20M	60
BUL53A		NPN	TO220	300	7			20M	125
BUL53B		NPN	TO220	250	10			20M	125
BUL54A		NPN	TO220	500	2			20M	125
BUL54B		NPN	TO220	400	2	12min	4/0.5	20M	35
BUL55A		NPN	TO220	300	4			20M	125
BUL55B		NPN	TO220	250	5				35
BUL98B	HR	NPN	TO3	400	25				
BUP30		NPN	TO220	30	20	70-300	2/1	120M	35
BUP31		PNP	TO220	30	20	70-300	2/1	120M	35
BUP32		NPN	SOT93	30	30	70-200	5/30	150M	60
BUP33		PNP	SOT93	30	30	70-200	5/30	150M	60
BUP34		NPN	TO220	900	1	30min	5/50m	6M	20
BUP35		NPN	SOT93	800	10	10min	5/1	15M	80
BUP36		NPN	SOT93	800	15	10min	2/1	15M	90
BUP37		NPN	SOT93	800	20	10min	2/1	15M	100
BUP38		NPN	SOT93	800	25	10min	2/1	15M	140
BUP39		NPN	SOT93	800	30	10min	2/1	15M	150
BUP42		NPN	TO220	500	10	10-50	2/1	18M	50
BUP43		NPN	SOT93	60	60	20min	4/60		150
BUP44		NPN	SOT93	100	50	15min	4/50		150
BUP45		NPN	SOT93	250	30	12min	4/30		200
BUP46	HR	NPN	TO3	60	60				250
BUP47	HR	NPN	TO3	100	50	15min	4/50		250
BUP48	HR	NPN	TO3	60	100	20min	4/40		250
BUP49	HR	NPN	TO3	80	90	20min	4/40		300
BUP50	HR	NPN	TO3	100	100	20min	4/40		300
BUP51	HR	NPN	TO3	175	80	20min	4/40		300
BUP52	HR	NPN	TO3	200	70	15min	4/40		300
BUP53	HR	NPN	TO3	250	60	10min	4/50		300
BUP54	HR	NPN	TO3	275	50	10min	4/40		300
BUP56		NPN	SOT93	60	30				150
BUP57		NPN	SOT93	100	25	20min	4/20		150
BUP58		NPN	SOT93	250	15	10min	4/15		150
BUP59		NPN	TO3	60	30	10min	4/15		200
BUR10	HR	NPN	TO66	80	5	40-120	5/2	50M	37
BUR11	HR	NPN	TO63	200	20	15min	5/15		175
BUR12	HR	NPN	TO59	120	10	80-140	5/1		40
BUR13	HR	NPN	TO63	125	70	20-100	5/25	40M	250
BUR20	CECC	NPN	TO3	125	50	10min	4/50	10M	250
BUR21	CECC	NPN	TO3	200	40	10min	4/25	10M	250
BUR22	CECC	NPN	TO3	250	40	10min	4/20	10M	250
BUR23	REQ	NPN	TO3	325	30				250
BUR24	REQ	NPN	TO3	400	30				250
BUR50	HR	NPN	TO3	125	70	15min	50/4	16	350
BUR50S	HR	NPN	TO3	125	70	15min	50/4	16	350
BUR51	HR	NPN	TO3	250	60	15min	4/40	16M	350
BUR51S	HR	NPN	TO3	250	60	15min	4/40	16M	350
BUS11	CECC	NPN	TO3	400	5	15min	5/1		100
BUS11A	CECC	NPN	TO3	450	5	15min	5/1		100
BUS12	CECC	NPN	TO3	400	8	15min	5/1		125
BUS12A	CECC	NPN	TO3	450	8	15min	5/1		125

HI-REL