

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CM	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			R	REVISED PER EC 0G3B-0151-99	10-APR-00</		

D

C

B




A

D

C

B

A



32.77

19.94

1. PARTS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-2.



CONTACT IS PLATED OVERALL WITH 0.00127 NICKEL, THEN 0.00076 GOLD OVER LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.

0.25 MAX
CUTOFF TAB


2.29

0.76

4.57

4.57
3.81

9.53



4.95
TYP
NON-ACCUM

RECOMMENDED MOUNTING HOLE PATTERN
FOR .062 THICK P.C. BOARD

METRIC

2.29	.090	-	-
1.78	.070	32.77	1.290
0.76	.030	19.94	.785
0.25	.010	9.53	.375
0.13	.005	9.14	.360
0.08	.003	4.95	.195
0.00127	.000050	4.57	.180
0.00076	.000030	3.81	.150
MM	IN	MM	IN
CONVERSION TABLE			

AMP 1471-9 REV 11 JUN97

CU ALLOY				NYLON, UL94V-0	NATURAL	350213-2	
CU ALLOY		PRE-TIN					

350213