


Model 5952A
Adjustable Tip Test Probe Set**FEATURES**

- Slim retractable probe fully insulated to within 1/8" (3,18) of tip
- Needle point tip adjusts to desired length from 0-3" (0-76mm)
- Stainless Steel needle point easily pierces varnish and thin insulation
- Tip can be re-pointed if necessary
- Multi-stacking Banana plug molded directly on the wire
- Banana plug spring is nickel plated Beryllium Copper for long insertion life
- 4 foot test lead wire is silicone insulated for high temperature resistance and flexibility at low temperature.
- Wear indication with double insulated (dual extruded) silicone leads shows black inner layer for increased safety.

MATERIALS

Probe Body: Polypropylene and PVC, color: one black, one red.

Tip: Stainless Steel

Wire: 20 AWG, Silicone insulation

RATINGS:

Operating Voltage: 30 Vrms/42.4 Vpk/60 Vdc

Current: 3 Amperes

ORDERING INFORMATION

Model 5952A

Includes a set of one black and one red test lead