




TYPICAL PERFORMANCE



Horizontal: 4 MHz/div

Vertical (from top):

Magnitude

10 dB/div

Magnitude

1 dB/div

Group Delay

50 ns./div


SPECIFICATION

Parameter	Min.	Typ.	Max.	Units.
Center Frequency (Fc) ¹	69.9	70.0	70.1	MHz
Insertion Loss at Fc		23.6	25	dB
1 dB Bandwidth	5.6	5.80		MHz
3 dB Bandwidth	6.0	6.20		MHz
40 dB Bandwidth		8.0	8.4	MHz
Passband Ripple		0.6	0.8	dB
Phase Ripple		3	7	deg p-p
Group Delay Ripple		80	130	ns p-p
Absolute Delay		3		us
Ultimate Rejection	50	60		dB
Substrate Material	112 Lithium Tantalate			
Ambient Temperature		25		° C

Notes:

1: Mean Value of 3 dB points

PACKAGE OUTLINE




Units: mm

Pin Configuration:

Input: 14
Input Return: 1
Output: 8
Output Return: 7
Ground: 2, 9

MATCHING CIRCUIT



Component values:

Ls1 = 270 nH Cp1 = 39 pF (Minimum Q = 45)
Ls2 = 300 nH Cp2 = 47 pF

Notes

1. Recommend use of 2% tolerance components.
2. Optimum Values depend on board layout. Values intended as guide only.

ISO 9001
Registered

Micro Networks

Worldwide Headquarters: 324 Clark Street Worcester, MA 01606. tel: 508-852-5400 fax: 508-852-8456
European Sales Headquarters: Hertosingel 20 6214 AD Maastricht, Netherlands. tel: +31-43-32-70912 fax: +31-43-32-70715
www.micronetworks.com