




△ TO BE MEASURED WITHIN 2mm FROM [-Z-]

2. APPLICABLE P.C.BOARD THICKNESS: 1.6mm

3. THE MATING COUNTERPART PART NUMBER: 174045,174046

4. RECOMMENDED MOUNTING SCREW: 3mmDIA, 6mmLENGTH TAPPING SCREW SPECIFIED IN JIS B1115,B1122. (TIGHTENING TORQUE;0.8N·M MAX.)

△ [-Z-]面より2mmの範囲で測定

2. 適用プリント基板厚: 1.6mm

3. 嵌合相手ハウジング型番: 174045,174046

4. 推奨取付ネジ: JIS B1115,B1122 タッピンネジ、ナベ2種 呼び径3、長さ6mm (締付けトルク0.8N·M以下)

断面 A-A

(SECT.A-A)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 特 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差

MATERIAL 材料 HOUSING: PBT CONTACT: BRASS

FINISH 仕上 -

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M.SUGAWARA 05JUL2006

CHK T.SHINOHARA 05JUL2006

APVD K.BETSUI 05JUL2006

PRODUCT SPEC 製品規格

APPLICATION SPEC 取付適用規格

WEIGHT 9g

CUSTOMER DRAWING

28POSITION CAP HOUSING ASSEMBLY

040 SERIES MULTI-LOCK I/O CONNECTOR

VERTICAL TYPE

SIZE A2

CAGE CODE 00779

DRAWING NO 番号 C=174979

RESTRICTED TO -

SCALE 2:1

SHEET 1 OF 1

REV D4

OBSELETE

OBSELETE

SELECTIVE-TIN

PRE-TIN

PRE-TIN

PRE-TIN

SELECTIVE-TIN (MATTE)

SELECTIVE-TIN (BRIGHT)

SOLDERING SIDE 半田付け部

CONTACT SIDE 接触部側

CONTACT FINISH コンタクト仕上

BLACK

BLUE

GREEN

BLACK

BLACK

COLOR 色

2-174979-2

174979-5

174979-4

174979-2

174979-1

PART NUMBER 製品型番

1471-9 (3/11)