




LOC	DIST	REVISIONS					
AP	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECO-11-005139	19MAR11	RK	HMR



DO NOT REVISE
EXCEPT BY CAD



SECTION B-B



SECTION A-A



PERSPECTIVE VIEW

- Ⓐ  - ELASTÔMERO SAE J 200 M 2BC 514, A14, B14, C12, E014, F17
- ELASTOMER SAE J 200 M 2BC 521, A14, B14, C12, E014, F17
- Ⓐ 2 - TOLERÂNCIA PARA REBARBAS / FLASH TOLERANCE:
COMPRIMENTO EXTERNO / OUTSIDE HEIGHT - 0,4mm MAX.
COMPRIMENTO INTERNO / INSIDE HEIGHT - 0,05mm MAX.
- Ⓐ 3 - USADO NO CONECTOR 282106-1, OU SIMILAR
- USED ON CONNECTOR 282106-1, OR SIMILAR

—	PRETO/BLACK		493581-1
RAW MAT'L NO.	FINISH	MATERIAL	PART NUMBER

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0,5 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°	DWN A. PERUSSI 03SEP98 CHK P. L. FARIA APVD J. M. M. NETO	 TE Connectivity	
MATERIAL SEE TABLE		FINISH SEE TABLE	PRODUCT SPEC -	NAME BOOT 4 POSN HSG	
			APPLICATION SPEC -	SIZE A3	CAGE CODE 00779
			WEIGHT -	DRAWING NO C- 493581	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 1:1	SHEET OF REV A1