



BLOW MOLDED CASE

Meet Platt's low cost solution to "Make-Your-Own" case needs. These cases are manufactured from prime, high-density polyethylene, with double wall construction. The textured exteriors resist dents, cracking and scuffs. The shells are unaffected by extreme temperatures. The hardware features mechanical latches that are field replaceable, and a mechanical hinge system that is made to last. All cases meet U.S. 94B Specifications as an electrical insulator and are impervious to chemical attack. All Platt Foam-Filled cases are filled with layers of cubed foam and a flat cushion in the bottom and convoluted and/or flat cushion in the lid.



Part Number	Outside Product Dimensions			Inside Product Dimensions		
	Length	Width	Depth	Length	Width	Depth
102	6 1/2"	4 1/2"	1 11/16"	5 5/8"	3 5/8"	1 3/8"
103	6 1/2"	4 1/2"	2 1/8"	5 5/8"	3 5/8"	1 7/8"
104	8"	5"	1 3/4"	7 1/8"	4"	1 3/4"
105	8"	5"	2 1/4"	7 1/8"	4"	1 15/16"
106	8 1/2"	6"	2"	7 1/2"	5"	1 11/16"
107	8 1/2"	6"	2 1/2"	7 1/2"	5"	2 3/16"
108	8 1/2"	6"	3"	7 1/2"	5"	2 11/16"
109	7"	4 3/8"	1 1/2"	6 3/16"	3 5/8"	1"
110	8"	5"	1 3/4"	7"	3 15/16"	1 7/16"
111	8"	5"	2 1/4"	7"	3 15/16"	1 11/16"
202	9 1/2"	6 1/2"	2"	8 1/2"	5 1/2"	1 11/16"
203	9 1/2"	6 1/2"	2 1/2"	8 1/2"	5 1/2"	2 3/16"
204	9 1/2"	6 1/2"	3"	8 1/2"	5 1/2"	2 11/16"
205	9 1/2"	6 1/2"	3 1/2"	8 1/2"	5 1/2"	3 3/16"
206	10 1/2"	7"	2 3/8"	9 1/2"	6"	1 15/16"

207	10 1/2"	7"	3"	9 1/2"	6"	2 11/16"
208	10 1/2"	7"	3 3/4"	9 1/2"	6"	3 7/16"
209	9"	5.5"	1 1/2"	7 5/16"	4 9/16"	1"
210	10 1/4"	6 1/4"	1 1/2"	9 1/2"	5 1/2"	1"
211	12 1/2"	7 1/4"	1 5/8"	11 11/16"	6 1/2"	1"
212*	12 1/8"	10 1/4"	2 7/8"	11 1/4"	9 3/8"	2 3/8"
302	11 5/16"	7 1/2"	2 1/4"	10 3/16"	6 1/2"	1 15/16"
303	11 5/16"	7 1/2"	3"	10 3/16"	6 1/2"	2 11/16"
304	11 5/16"	7 1/2"	3 3/4"	10 3/16"	6 1/2"	3 7/16"
305	12"	8"	2 1/4"	11"	7"	1 15/16"
306	12"	8"	3"	11"	7"	2 11/16"
307	12"	8"	3 3/4"	11"	7"	3 7/16"
308	13 1/2"	8"	3 1/4"	12 3/8"	6 7/8"	2 7/8"
309	13 1/2"	8"	4 3/8"	12 3/8"	6 7/8"	4 1/16"
310	13 1/2"	8"	5 1/2"	12 3/8"	6 7/8"	5 3/16"
402	13 1/2"	9"	3 1/4"	12 3/8"	7 7/8"	2 7/8"
403	13 1/2"	9"	4 3/8"	12 3/8"	7 7/8"	4"
404	13 1/2"	9"	5 1/2"	12 3/8"	7 7/8"	5 1/8"
405	13 1/2"	10"	3 1/4"	12 3/8"	8 7/8"	2 7/8"
406	13 1/2"	10"	4 3/8"	12 3/8"	8 7/8"	4"
407	13 1/2"	10"	5 1/2"	12 3/8"	8 7/8"	5 1/8"
408*	13 1/2"	11"	3 1/4"	12 1/2"	10"	2 15/16"
409	14"	9"	2 3/8"	13"	8"	2 1/4"
501	15"	5"	2 1/2"	14"	4"	2 3/16"
502WT	15"	11"	4 3/8"	13 7/8"	9 7/8"	4"

503	15"	10"	3 1/4"	13 7/8"	8 7/8"	2 7/8"
504	15"	10"	4 3/8"	13 7/8"	8 7/8"	4"
505	15"	10"	5 1/2"	13 7/8"	8 7/8"	5 1/8"
506	15"	11"	3 1/4"	13 7/8"	9 7/8"	2 7/8"
507	15"	11"	4 3/8"	13 7/8"	9 7/8"	4"
508	15"	11"	5 1/2"	13 7/8"	9 7/8"	5 1/8"
509*	15"	11"	3 1/4"	14"	10"	2 5/16"
604	16"	11 1/2"	3 1/4"	14 7/8"	10 3/8"	2 7/8"
605	16"	11 1/2"	4 3/8"	14 7/8"	10 3/8"	4"
606	16"	11 1/2"	5 1/2"	14 7/8"	10 3/8"	5 1/8"
607	17"	12"	3 1/4"	15 7/8"	10 7/8"	2 7/8"
608	17"	12"	4 3/8"	15 7/8"	10 7/8"	4"
609	17"	12"	5 1/2"	15 7/8"	10 7/8"	5 1/8"
610	18"	13"	4 1/4"	16 7/8"	11 11/16"	3 7/8"
611	18"	13"	5 3/8"	16 7/8"	11 11/16"	5"
612	18"	13"	6 1/2"	16 7/8"	11 11/16"	6 1/8"
613	17"	7"	3 1/4"	16"	6"	2 15/16"
704WT	19"	14"	6 1/8"	18"	13"	5 1/8"
705	19"	14"	4 3/4"	17 7/8"	12 11/16"	4 3/8"
706	19"	14"	6 1/4"	17 7/8"	12 11/16"	5 3/4"
707	19"	14"	7 1/2"	17 7/8"	12 11/16"	7 1/8"
708	23"	15"	4 5/16	21 11/16"	13 11/16"	3 15/16"
709	23"	15"	5 5/8"	21 11/16"	13 11/16	5 1/4"
801	21"	8"	2 1/2"	20"	7"	2 3/16"
802*	23"	16"	7"	21 1/2"	14"	6 5/8"

803*	23"	16"	10"	21 5/16	14 5/16	9 5/8"
901	28"	9"	4 1/2"	26 1/4"	7 3/4"	4 3/16
902*	27 1/2"	16"	7"	25 13/16"	14 5/16"	6 5/8"
903*	27 1/2"	16"	10"	25 13/16"	14 5/16"	9 5/8"

***Molded-in Handle reduces "W" dimension usable space.
Please contact Platt Engineering Department for more information.**