


PRINT DIST



RETENTION LEG  CONTACT 半田付部 CONTACT TAIL	X-X KEY	注 記 1. 材料: ハウジング: ガラス入り熱可塑性 ポリエステル樹脂 (94V-0), 色: 黒 コンタクト: 銅合金 リテンションレグ: 銅合金										
		 めっき: コンタクト: 全面Ni下地 接触部: 0.38μm MIN金めっき										
		 めっき: コンタクト: 全面Ni下地 接触部: 0.76μm MIN金めっき										
NOTES 1. MATERIAL:HOUSING:GLASS FILLED THERMO PLASTIC,POLYESTER(94V-0),COLOR:BLACK CONTACT:COPPER ALLOY RETENTION LEG:COPPER ALLOY		 めっき: コンタクト: 全面Ni下地 接触部: 2.0 μm MINスズめっき										
 FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING OVER Ni PLATING		 めっき: リテンションレグとコンタクト半田付部 ニッケル下地の上に半田めっき										
 FINISH(CONTACT AREA):0.76μmMIN GOLD PLATING OVER Ni PLATING		 めっき: リテンションレグとコンタクト半田付部 : ニッケル下地										
 FINISH(CONTACT AREA):2.0 μmMIN TIN PLATED OVER NICKEL												
 FINISH(RETENTION LEG): TIN LEAD PLATED (CONTACT TAIL) OVER NICKEL												
 FINISH(RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL												
 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI		<table border="1"> <tr> <td>B4</td><td>REVISED PER ECO-11-005030</td><td>RK</td><td>HMR</td><td>20MAR 11</td></tr> <tr> <td>LTR</td><td>REVISION RECORD</td><td>DR</td><td>CHK</td><td>DATE</td></tr> </table>	B4	REVISED PER ECO-11-005030	RK	HMR	20MAR 11	LTR	REVISION RECORD	DR	CHK	DATE
B4	REVISED PER ECO-11-005030	RK	HMR	20MAR 11								
LTR	REVISION RECORD	DR	CHK	DATE								

B ROW		X	Y		3-316081-5
A ROW					3-316081-3
					3-316081-2
B ROW		Y	Y		2-316081-5
A ROW					2-316081-3
					2-316081-2
B ROW		X	X		1-316081-5
A ROW					1-316081-3
					1-316081-2
KEYING LOCATION		A ROW KEYING	B ROW KEYING	FINISH	製品番号 PART NO.

TE Connectivity

WIRE RANGE mm ² (AWG) - mm ²		INSULATION DIA. - mm ϕ		NAME 12 POS DOUBLE ROW HORIZONTAL HDR ASS'Y FOR DYNAMIC D-3200	
MATERIAL SEE NOTE 注記参照	FINISH SEE NOTE 注記参照	一般公差 (GENERAL TOLERANCE) 10% : ±0.3 10% 30% : ±0.4 30% 100% : ±0.45 角度 : ±3°		SIZE A3	LOC J
DR. K.IKEDA 4/7 JUL/'95	DE. K.IKEDA 4/7 JUL/'95			NUMBER C=316081	
CHK. Y.ISHIKAWA 4/7 JUL/'95	APP. S.MANABE 4/7 JUL/'95			SCALE 2-1	REV. B4
				SHEET 7 OF 7	